



1-Piece Fixing Ties with Arrowhead, with Wings in the strap T80RSF6.5F

T80RSF6.5F, Article number: 126-02600



Images (5)

Downloads



Features

- Easy to assemble without the need for a tool
- Arrowhead simply locks into place
- Supporting legs provide a secure and firm fixing in areas where space is limited
- Bundle runs central across fixing point
- Cable tie head always situated in defined position
- For parallel routing of two bundles

Certifications & Approvals



Application

This range of fixing ties is ideal for use in many different industries, including automotive, aerospace and panel building. The T80RSF6.5FW features a detent that fits securely into the profile of the tubing which prevents from lateral movement and slipping.

T80RSF6.5F is suitable for following markets and industries

- Solar Energy Sector
- Wind Energy Sector
- Rail Transportation Sector
- Automotive Industry
- Electronics Industry
- Shipbuilding
- Defence Industry

More products in this product group

[1-Piece Fixing Ties with Arrowhead, with Wings in the strap >](#)

Base Data

Anti rotation (Yes / No)	NO
Application Tool	MK3PNSP2, MK3SP, MK7P, MK20, EVO7, EVO7SP
Colour	Black (BK)
Description Short (BMEcat) (max. 150 characters)	1-Piece Fixing Tie with Arrowhead and Wings in the strap PA66HS 209x4.7 black
Fixation Method	Arrowhead
Fixing Hole Shape	Circular
GLOBAL PART DESCRIPTION	T80RSF6.5F-PA66HS-BK
Identification Plate Position	none
Pack Cont.	1000 pcs.
Package Quantity per	pcs.
Product Family	T80RSF6.5F
Product Group	1-Piece Fixing Ties with Arrowhead, with Wings in the strap
Releasable Closure	No

Tie Closure	plastic pawl
Variant	Inside Serrated

Product Dimensions



Bundle $\varnothing$ max.	50.0 mm
for Hole $\varnothing$ (FH)	6.3 - 6.5 mm
for Panel Thickness min - max	0.6 - 3 mm
for Panel Thickness min - max	0 - 0 "
Height (H)	1.27 mm
Length (L)	209 mm
Length of Fir Tree	7.6 mm
Min.Tensile Strength	355 N
Thickness (T)	1.3 mm
Width (W)	4.7 mm

Material and Specifications



ELV compliant (Article 4 - 2)	YES
Hazardous good	No
Material	Polyamide 6.6, heat stabilised (PA66HS)
Operating Temperature - °C	-40 °C to +105 °C, (+145 °C, 500 h)
Specifications	

Logistics and Packaging




More Information



ETIM 5.0	EC000046
ETIM 6.0	EC000046
UNSPSC Key	39121717


Further information to T80RSF6.5F



Technical drawing
14.1349



Download >



Technical drawing
14.1350



Download >



CAD-Download

Download >

Competences



Cable Ties and Fixings

Cable ties have to be able to meet the most varied demands these days as they are used in the widest range of operations – from the simple bundling of cables with cable ties to the absolutely specific use of cable ties under extreme conditions.

[Cable Ties >](#)

Accessories



EVO7
110-70129
Manual tensioning tool
plastic housing



EVO7SP
110-70130
Manual Tensioning Tool
Plastic Housing



MK3PNSP2
110-03400
Pneumatic tensioning
tool metal housing



MK7P
110-07100
Pneumatic tensioning
tool plastic housing



MK20
110-20006
Manual tensioning tool
for cable ties, simple
version



MK3SP
110-03500
Manual tensioning tool
metal housing

Similar products



T80RSF6.5F
150-39395
1-Piece Fixing Ties with
Arrowhead, with Wings
in the strap



T80RSF6.5F
126-00093
1-Piece Fixing Ties with
Arrowhead, with Wings
in the strap



T80RSF6.5F
126-00094
1-Piece Fixing Ties with
Arrowhead, with Wings
in the strap

Stay in touch with us!



Global Company

About us
Worldwide
Philosophy
Environment & Quality
Corporate Social
Responsibility
Product Development
E-Business
ACADEMY
Careers
MADE FOR REAL

Products

Product overview
Cable Ties and Fixings
Insulation
Cable Protection Systems
Electrical Installation
Identification Systems
Application Tooling
Connectivity

Competences

Cable Ties
Heat Shrink Tubing
Industrial Identification
and Self-Adhesive Labels
Cable Protection
Conduits
Electrical Installation
Electrical tape
Wire connectors
Cable rods
Downlight covers
Cable jointing
Gel-filled cable joints
Cable Tie Guns
Connectivity Products
RFID tracking
Cable tie mounts
Thermal Transfer Printer
P-Clamp
Wiring ducts
Cable clips for edges

Markets & Industries

Automotive Industry
Solar plants
Wind turbines
Shipbuilding
Panel building
Rail industry
Food Industry
Chemical Industry
Aerospace Industry
Defence Industry

Media Centre

Videos
Product Catalogue
2018/2019
Automotive Catalogue
2016/2017
Connectivity Catalogues
2016/2017
Brochures
Software & Drivers
Helatag & Helafix
Templates
Manuals & Operating
Instructions

Cable management high
temperature
applications

Events

Update: 07/10/2018

You can easily accept or reject the cookies on this site by choosing one of the following links:

[I accept cookies](#)

[I refuse cookies](#)

[Privacy](#)

[Contact](#) [Terms of Service](#) [Imprint](#) [Privacy Policy](#)

[statement](#)