



Quality Products. Service Excellence.

## Outdoor FilterFans 3RFF Series

Type 3R

NEW



### Features

- Designed for outdoor weather where resistance against falling rain, ice formation, and UV degradation is important to ensure operation of apparatus inside enclosure.
- Maintains a UL Tested NEMA Type 3R seal against enclosure without need of a rainhood.
- Patented "Click & Fit" design provides a hardware-free installation.
- Plastic made from strong, heat resistant UL 94 V0 fire approved ABS material.
- Fluted filter-mat provides longer service life, holding more dust before impeding airflow extending the mean time between maintenance for outdoor enclosure, which can be especially critical for those located in remote areas.
- Offered in Light Gray (RAL 7035) and Black (RAL 9011).

### Accessories

- Exhaust Filters
- Thermostats
- Replacement Filters



| Part Number        | Part Number     | Free Flow |     |       |       | Exhaust Filter |                    |
|--------------------|-----------------|-----------|-----|-------|-------|----------------|--------------------|
| Light Gray RAL7035 | Black RAL9011   | Voltage   | CFM | H     | W     | D              | Light Gray RAL7035 |
| PF22000T3RLG       | PF22000T3RBK    | 115 VAC   | 38  | 5.71  | 5.71  | 2.76           | PFA20000T3RLG      |
| PF22000T3RLG230    | PF22000T3RBK230 | 230 VAC   | 38  | 5.71  | 5.71  | 2.76           | PFA20000T3RLG      |
| PF22000T3RLG24     | PF22000T3RBK24  | 24 VDC    | 38  | 5.71  | 5.71  | 2.76           | PFA20000T3RLG      |
| PF32000T3RLG       | PF32000T3RBK    | 115 VAC   | 65  | 7.95  | 7.95  | 3.66           | PFA30000T3RLG      |
| PF32000T3RLG230    | PF32000T3RBK230 | 230 VAC   | 65  | 7.95  | 7.95  | 3.66           | PFA30000T3RLG      |
| PF32000T3RLG24     | PF32000T3RBK24  | 24 VDC    | 65  | 7.95  | 7.95  | 3.66           | PFA30000T3RLG      |
| PF42500T3RLG       | PF42500T3RBK    | 115 VAC   | 94  | 9.92  | 9.92  | 4.05           | PFA40000T3RLG      |
| PF42500T3RLG230    | PF42500T3RBK230 | 230 VAC   | 94  | 9.92  | 9.92  | 4.05           | PFA40000T3RLG      |
| PF42500T3RLG24     | PF42500T3RBK24  | 24 VDC    | 94  | 9.92  | 9.92  | 4.05           | PFA40000T3RLG      |
| PF43000T3RLG       | PF43000T3RBK    | 115 VAC   | 155 | 9.92  | 9.92  | 4.05           | PFA40000T3RLG      |
| PF43000T3RLG230    | PF43000T3RBK230 | 230 VAC   | 155 | 9.92  | 9.92  | 4.05           | PFA40000T3RLG      |
| PF43000T3RLG24     | PF43000T3RBK24  | 24 VDC    | 155 | 9.92  | 9.92  | 4.05           | PFA40000T3RLG      |
| PF65000T3RLG       | PF65000T3RBK    | 115 VAC   | 297 | 12.60 | 12.60 | 6.18           | PFA60000T3RLG      |
| PF65000T3RLG230    | PF65000T3RBK230 | 230 VAC   | 297 | 12.60 | 12.60 | 6.18           | PFA60000T3RLG      |
| PF66000T3RLG       | PF66000T3RBK    | 115 VAC   | 462 | 12.60 | 12.60 | 6.18           | PFA60000T3RLG      |
| PF66000T3RLG230    | PF66000T3RBK230 | 230 VAC   | 462 | 12.60 | 12.60 | 6.18           | PFA60000T3RLG      |
| PF66000T3RLG460    | PF66000T3RBK460 | 460 VAC   | 462 | 12.60 | 12.60 | 6.18           | PFA60000T3RLG      |
| PF67000T3RLG       | PF67000T3RBK    | 115 VAC   | 560 | 12.60 | 12.60 | 6.18           | PFA60000T3RLG      |
| PF67000T3RLG230    | PF67000T3RBK230 | 230 VAC   | 560 | 12.60 | 12.60 | 6.18           | PFA60000T3RLG      |

| Part Number        |  | Part Number     |  | Free Flow |     |       | Exhaust Filter |      | Exhaust Filter     |
|--------------------|--|-----------------|--|-----------|-----|-------|----------------|------|--------------------|
| Light Gray RAL7035 |  | Black RAL9011   |  | Voltage   | CFM | H     | W              | D    | Light Gray RAL7035 |
| PF67000T3RLG460    |  | PF67000T3RBK460 |  | 460 VAC   | 560 | 12.60 | 12.60          | 6.18 | PFA60000T3RLG      |
|                    |  |                 |  |           |     |       |                |      | PFA60000T3RBK      |

Tags: **Type 3R**, **filterfan**, **fan**, **filter**, **UV**, **outdoor**, **rain**, **ice**

*Data subject to change without notice*