

SB 2-URTK/SP - Bridge bar



0360012

<https://www.phoenixcontact.com/us/products/0360012>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bridge bar, pitch: 8.2 mm, number of positions: 2, color: silver-colored



Commercial data

Item number	0360012
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z3X
GTIN	4017918001742
Weight per piece (including packing)	5.66 g
Weight per piece (excluding packing)	5.6 g
Customs tariff number	85369095
Country of origin	PL

SB 2-URTK/SP - Bridge bar



0360012

<https://www.phoenixcontact.com/us/products/0360012>

Technical data

Product properties

Product type	Bridge bar
Number of positions	2
Pitch	8.2 mm
Potentials	1

Connection data

Tightening torque	1.2 ... 1.5 Nm
-------------------	----------------

Dimensions

Pitch	8.2 mm
-------	--------

Material specifications

Color	silver-colored
Material	Copper

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	Screw mounting
---------------	----------------

SB 2-URTK/SP - Bridge bar



0360012

<https://www.phoenixcontact.com/us/products/0360012>

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 9.0	EC000489
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SB 2-URTK/SP - Bridge bar



0360012

<https://www.phoenixcontact.com/us/products/0360012>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com