HIGH-VOLTAGE POWER SCHOTTKY RECTIFIER

Product Summary

V_{RRM} (V)	I_O (A)	$V_{F\ (MAX)}$ (V) @ 25°C	$I_{R\ (MAX)}$ (mA) @ 25°C
100	2 × 10	0.85	0.1

Description

High-voltage dual Schottky rectifier suited for switch mode power supplies and other power converters. This device is intended for use in medium-voltage operation, and particularly, in high-frequency circuits where low switching losses and low noise are required.

The MBR20100C is available in TO-220-3 (2), TO220AB (Type WX), TO-220F-3, and ITO220AB (Type WX) packages.

Features

- Low Forward Voltage: 0.85V @ +25°C
- High Surge Current Capability
- +150°C Operating Junction Temperature
- 20A Total (10A Each Diode Leg)
- Guard-Ring for Stress Protection
- **Lead-Free Finish; RoHS Compliant (Notes 1 & 2)**
- **Halogen and Antimony Free. "Green" Device (Note 3)**
- **For automotive applications requiring specific change control (i.e. parts qualified to AEC-Q100/101/104/200, PPAP capable, and manufactured in IATF 16949 certified facilities), please contact us or your local Diodes representative. https://www.diodes.com/quality/product-definitions/**

Applications


- Power supply output rectification
- Power management
- Instrumentation

Mechanical Data


- Package: TO-220-3 (2), TO220AB, TO-220F-3, and ITO220AB
- Package Material: Molded Plastic, "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Terminals: Finish – Matte Tin Annealed over Copper Leadframe. Solderable per MIL-STD-202, Method 208 e3
- Polarity: See Below
- Weight:
  - TO-220-3 (2), TO220AB: 1.9 grams (Approximate)
  - TO-220F-3, ITO220AB: 1.69 grams (Approximate)




TO-220F-3



ITO220AB (Type WX)



TO-220-3 (2)



TO220AB (Type WX)


Notes:
1. EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant. All applicable RoHS exemptions applied.
2. See https://www.diodes.com/quality/lead-free/ for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.


Pin Assignments

(Front View)




TO-220-3 (2)

(Front View)




TO-220F-3




Internal Structure of MBR20100C

(Front View)



TO220AB (Type WX)

(Front View)



ITO220AB (Type WX)

Ordering Information (Note 4)

MBR20100C XX XX - XX

Product Name	Package	Packing	RoHS/Green
	T: TO-220-3 (2) TO220AB (Type WX) TF: TO-220F-3 ITO220AB (Type WX)	Blank : Tube	G1 : RoHS Compliant and Green

Orderable Part Number	Package	Marking ID	Packing	
			Qty.	Carrier
MBR20100CT-G1	TO-220-3 (2)	MBR20100CT-G1	50 Pieces	Tube
MBR20100CT-G1	TO220AB (Type WX)	MBR20100CT-G1	50 Pieces	Tube
MBR20100CTF-G1	TO-220F-3	MBR20100CTF-G1	50 Pieces	Tube
MBR20100CTF-G1	ITO220AB (Type WX)	MBR20100CTF-G1	50 Pieces	Tube


Note: 4. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Marking Information

(1) TO-220-3 (2), TO220AB (Type WX)


(Front View)



First and Second Lines: Logo and Marking ID
(See *Ordering Information*)
Third Line: Date Code
Y: Year
WW: Work Week of Molding
A: Assembly House Code (Optional)
XX: 7th and 8th Digits of Batch Number

(2) TO-220F-3, ITO220AB (Type WX)

(Front View)



First and Second Lines: Logo and Marking ID
(See *Ordering Information*)
Third Line: Date Code
Y: Year
WW: Work Week of Molding
A: Assembly House Code (Optional)
XX: 7th and 8th Digits of Batch Number

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Maximum Ratings (Each Diode Leg)

Characteristic	Symbol	Rating	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V_{RRM} V_{RWM} V_R	100	V
Average Rectified Forward Current (Rated V_R) T_C = 122°C	$I_{F(AV)}$	10	A
Peak Repetitive Forward Current (Rated V_R, Square Wave, 20kHz) T_C = 118°C	I_{FRM}	20	A
Non-Repetitive Peak Surge Current (Surge Applied at Rated Load Conditions Half Wave, Single Phase, 60Hz)	I_{FSM}	150	A
Non-Repetitive Peak Reverse Current, t_P = 3µs	I_{RSM}	2	A
Operating Junction Temperature (Note 5)	T_J	150	°C
Storage Temperature Range	T_{STG}	-65 to 150	°C
Voltage Rate of Change (Rated V_R)	dv/dt	10000	V/µs
ESD (Machine Model = C)	—	> 400	V
ESD (Human Body Model = 3B)	—	> 8000	V

Note: 5. The heat generated must be less than the thermal conductivity from Junction to Ambient: $dP_D/dT_J < 1/\theta_{JA}$.

Thermal Characteristics

Characteristic	Symbol	Rating		Unit
Maximum Thermal Resistance (Junction to Case) (Note 6)	$R_{\theta JC}$	TO-220-3 (2) TO220AB (Type WX)	2.5	°C/W
		TO-220F-3 ITO220AB (Type WX)	4.5	
Maximum Thermal Resistance (Junction to Ambient) (Note 6)	$R_{\theta JA}$	TO-220-3 (2) TO220AB (Type WX)	60	°C/W
		TO-220F-3 ITO220AB (Type WX)	60	

Note: 6. Device mounted on heatsink, with minimum recommended pad layout per http://www.diodes.com/package-outlines.html.

Electrical Characteristics

Characteristic	Symbol	Rating	Unit	Test Condition
Maximum Instantaneous Forward Voltage Drop (Note 7)	V_F	0.85	V	I_F = 10A, T_C = 25°C
		0.75		I_F = 10A, T_C = 125°C
Maximum Instantaneous Reverse Current (Note 7)	I_R	6.0	mA	Rated DC Voltage, T_C = 125°C
		0.1		Rated DC Voltage, T_C = 25°C

Note: 7. Short duration pulse test used to minimize self-heating effect. Pulse test width = 300µs, duty cycle < 2.0%.

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.




Figure 1. Typical Forward Voltage Per Diode




Figure 2. Typical Reverse Current Per Diode





Figure 3. Average Rectified Forward Current vs. Case Temperature (Per Diode)

© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Package Outline Dimensions (All dimensions in mm(inch).)

Please see http://www.diodes.com/package-outlines.html for the latest version.

(1) Package Type: TO-220-3 (2)




© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Package Outline Dimensions (continued)

Please see http://www.diodes.com/package-outlines.html for the latest version.

(2) Package Type: TO220AB (Type WX)



TO220AB (Type WX)		
Dim	**Min**	**Max**
A	3.56	4.83
A1	1.14	1.40
A2	2.03	2.92
b	0.51	1.14
b1	1.14	1.70
c	0.30	0.64
D	14.40	15.20
D1	8.26	9.28
E	9.65	10.67
e	2.29	2.79
H1	5.84	6.86
L	12.70	14.73
L1	--	4.20
PØ	3.53	4.09
Q	2.54	3.43
All Dimensions in mm		


© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

Package Outline Dimensions (continued) (All dimensions in mm(inch).)

Please see http://www.diodes.com/package-outlines.html for the latest version.

(3) Package Type: TO-220F-3




© 2026 Copyright Diodes Incorporated. All Rights Reserved.
Downloaded from Arrow.com.

Package Outline Dimensions (continued)

Please see http://www.diodes.com/package-outlines.html for the latest version.

(4) Package Type: ITO220AB (Type WX)



ITO220AB (Type WX)		
Dim	**Min**	**Max**
A	4.46	4.87
A1	2.48	2.80
A2	2.50	2.80
b	0.50	0.80
b1	1.15	1.70
b2	1.50	1.90
c	0.45	0.70
D	14.95	15.95
D1	8.50	8.80
E	10.00	10.40
e	2.40	2.70
L	13.00	13.70
L1	3.30	3.90
Q	2.76	3.36
P	3.00	3.30
All Dimensions in mm		

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.

IMPORTANT NOTICE

1. DIODES INCORPORATED (Diodes) AND ITS SUBSIDIARIES MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes' products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes' products. Diodes' products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of Diodes' products for their intended applications, (c) ensuring their applications, which incorporate Diodes' products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.

3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.

4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.

5. Diodes' products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.

6. Diodes' products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes' products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.

7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.

8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

9. This Notice may be periodically updated with the most recent version available at https://www.diodes.com/about/company/terms-and-conditions/important-notice

The Diodes logo is a registered trademark of Diodes Incorporated in the United States and other countries.
All other trademarks are the property of their respective owners.
© 2026 Diodes Incorporated. All Rights Reserved.

www.diodes.com

© 2026 Copyright Diodes Incorporated. All Rights Reserved.

Downloaded from Arrow.com.