



### Equipment Jumper Kits

- Bond network equipment to grounding strip or grounding busbar
- Jumper kit available with both ends factory terminated to provide a bolt-on solution
- Jumper kit available with one end factory terminated to attach to the grounding strip or grounding busbar; free end accommodates unique equipment terminations

- Use jumpers with 90° bent lug, on grounding strip side, for high density grounding requirements up to one ground point per RU
- Use jumpers with 45° bent lugs, on grounding strip side, for improved cable management
- Engineered to comply with US and International grounding requirements



RGEJ1024PFY



RGEJ1057PFY



| Part Number                                                                                                              | Length<br>In.<br>(m) | Angle    | Part Description                                                                                                                                                                                                                        | Std.<br>Pkg.<br>Qty. | Std.<br>Ctn.<br>Qty. |
|--------------------------------------------------------------------------------------------------------------------------|----------------------|----------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------|----------------------|
| <b>#6 AWG (16mm<sup>2</sup>) Equipment Jumper Factory Terminated on One End for Switches, Cabinets, and 4-Post Racks</b> |                      |          |                                                                                                                                                                                                                                         |                      |                      |
| GJS660U                                                                                                                  | 60<br>(1.52)         | Straight | #6 AWG green wire with yellow horizontal stripe. Jumper is pre-terminated on one end with LCC6-14JAW-L.                                                                                                                                 | 1                    | 10                   |
| GJS696U                                                                                                                  | 96<br>(2.44)         | Straight |                                                                                                                                                                                                                                         | 1                    | 10                   |
| <b>#10 AWG (6mm<sup>2</sup>) Equipment Jumpers Factory Terminated on Both Ends</b>                                       |                      |          |                                                                                                                                                                                                                                         |                      |                      |
| RGEJ1024PHY                                                                                                              | 24<br>(0.61)         | 45°      | #10 AWG (6mm <sup>2</sup> ) jumper; bent lug on grounding strip side to straight lug on equipment; provided with .16 oz. (5cc) of antioxidant and two each #12-24 x 1/2", M6 x 12mm, #10-32 x 1/2" and M5 x 12mm thread-forming screws. | 1                    | 10                   |
| RGEJ1024PFY                                                                                                              | 24<br>(0.61)         | 90°      |                                                                                                                                                                                                                                         | 1                    | 10                   |
| RGEJ1036PFY                                                                                                              | 36<br>(0.91)         | 90°      |                                                                                                                                                                                                                                         | 1                    | 10                   |
| RGEJ1024URT*                                                                                                             | 24<br>(0.61)         | Straight | #10 AWG (6mm <sup>2</sup> ) jumper, 24 in. (609.6mm) L, pre-terminated with two #10 (5.3mm) stud hole ring terminals to provide a bolt-on solution for grounding network equipment.                                                     | 1                    | 10                   |
| <b>#6 AWG (16mm<sup>2</sup>) Equipment Jumpers Factory Terminated on Both Ends</b>                                       |                      |          |                                                                                                                                                                                                                                         |                      |                      |
| RGEJ624PHY                                                                                                               | 24<br>(0.61)         | 45°      | #6 AWG (16mm <sup>2</sup> ) jumper; bent lug on grounding strip side to straight lug on equipment; provided with .16 oz. (5cc) of antioxidant and two each #12-24 x 1/2", M6 x 12mm, #10-32 x 1/2" and M5 x 12mm thread-forming screws. | 1                    | 10                   |
| RGEJ624PFY                                                                                                               | 24<br>(0.61)         | 90°      |                                                                                                                                                                                                                                         | 1                    | 10                   |
| RGEJ636PFY                                                                                                               | 36<br>(0.91)         | 90°      |                                                                                                                                                                                                                                         | 1                    | 10                   |
| RGEJ660U*                                                                                                                | 60<br>(1.52)         | Straight | #6 AWG (16mm <sup>2</sup> ) jumper, 60 in. (1524mm) L, pre-terminated with two straight slotted lugs to provide a bolt-on solution for grounding network equipment.                                                                     | 1                    | 10                   |
| RGEJ696U*                                                                                                                | 96<br>(2.44)         | Straight | #6 AWG (16mm <sup>2</sup> ) jumper, 96 in. (2438.4mm) L, pre-terminated with two straight slotted lugs to provide a bolt-on solution for grounding network equipment.                                                                   | 1                    | 10                   |
| <b>#10 AWG (6mm<sup>2</sup>) Equipment Jumper Factory Terminated on One End</b>                                          |                      |          |                                                                                                                                                                                                                                         |                      |                      |
| RGEJ1057PFY                                                                                                              | 57<br>(1.45)         | 90°      | #10 AWG (6mm <sup>2</sup> ) jumper; bent lug on grounding strip side; provided with .16 oz. (5cc) of antioxidant and two each #12-24 x 1/2", M6 x 12mm, #10-32 x 1/2" and M5 x 12mm thread-forming screws.                              | 1                    | 10                   |
| <b>#6 AWG (16mm<sup>2</sup>) Equipment Jumper Factory Terminated on One End</b>                                          |                      |          |                                                                                                                                                                                                                                         |                      |                      |
| RGEJ657PFY                                                                                                               | 57<br>(1.45)         | 90°      | #6 AWG (16mm <sup>2</sup> ) jumper; bent lug on grounding strip side; provided with .16 oz. (5cc) of antioxidant and two each #12-24 x 1/2", M6 x 12mm, #10-32 x 1/2" and M5 x 12mm thread-forming screws.                              | 1                    | 10                   |

An equal number of M6 x 12mm thread-forming screws also provided in each kit.

\*For use with VBlock preconfigured solutions.

A.  
System  
Overview

B.  
Copper  
Systems

C.  
Fiber  
Optic  
Systems

D.  
Power  
over  
Ethernet

E.  
Zone  
Cabling

F.  
Wireless

G.  
Outlets

H.  
Media  
Distribution

I.  
Physical  
Infrastructure  
Management

J.  
Overhead &  
Underfloor  
Routing

K.  
Surface  
Raceway

L.  
Cabinets,  
Racks &  
Cable  
Management

M.  
Grounding &  
Bonding

N.  
Industrial

O.  
Labeling &  
Identification

P.  
Cable  
Management  
Accessories

Q.  
Index