

Dual Mode SSHB Coils, 10HS Series, Wide Range Impedance Type

Overview

The KEMET SSHB coils are dual mode chokes with a wide variety of characteristics. These hybrid coils combine the two functions of normal mode countermeasure and common mode noise suppression, with just one coil. Reducing the number of required products ensures cost savings and space efficiency. Our proprietary core materials provide optimized solutions for high-temperature requirements (standard type) or for high permeability needs (R type). In addition, the specially developed shape is efficient with normal noise suppression.

Applications

- LED lighting
- Audio-visual equipment
- Office automation equipment
- Power supplies

Benefits

- Proprietary 5HT and 10H ferrite materials and equivalents
- Optimization of magnetic circuit and material
- One coil to suppress both common and normal noise
- High impedance in wide frequency range due to divided bobbin
- High permeability for R type
- Operating temperature range from -40°C to +130°C for standard type
- Operating temperature range from -40°C to +120°C for R type
- Low leakage magnetic flux to outside
- Compact size and low height
- UL 94 V-0 flame retardant rated base and bobbin



Part Number System

SSHB	10	HS-	R	04	620
Series	Core Size Code	Core Orientation and Bobbin Type	Core Type	Rated Current (A)	Inductance (mH) Minimum
SSHB	10	HS = Horizontal, bobbin with sectional winding structure	Blank = Standard R = High permeability	0x = 0.x A xx = x.x A Examples: 03 = 0.3 A 13 = 1.3 A	xx0 = xx mH xxx = xx.x mH 0xx = x.x mH Examples: 620 = 62 mH 122 = 12.2 mH 071 = 7.1 mH

Built Into Tomorrow

Magnetic Permeability of Ferrite Material

In order to achieve efficient noise reduction, it is important to select the material according to the target frequency band.

Depending on its magnetic permeability, a particular ferrite material will be effective in a certain frequency band.


A schematic representation of the relationship between the magnetic permeability of each material and the corresponding effective band range is shown in Figure 1.

Materials with higher magnetic permeability are effective in the lower frequency range, while those with lower magnetic permeability are effective in the higher frequency range. Thus, Mn-Zn products are mainly used for reducing conduction noise, while Ni-Zn products are commonly used for radiation noise countermeasures.

The effective frequency range varies depending on core shape, size and number of windings. This frequency dependence of the magnetic permeability as shown in the figure serves for reference purposes only and it should be tested on the actual device to determine its effectiveness.

S18H, S15H, 10H, 7H, 5H, 5HT, 1400L and 700L are KEMET's proprietary ferrite material names. Other materials can also be available on request.

Figure 1 - Relationship between the magnetic permeability of each material and its effective frequency range



Core Structure




Conventional




Original New Core Shape

This original shape structure allows for optimized composite characteristics of common mode and normal mode noise countermeasures.

Magnetic Flux Density




Common Mode



Normal Mode

- › Increased efficiency on normal mode inductance
- › Material solution for specific requirements
 - ✓ Standard type for high temperature needs
 - ✓ R type for high permeability needs
- › Low leakage magnetic flux to outside

Dimensions – Millimeters



Environmental Compliance

All KEMET AC Line Filters are RoHS Compliant.



Performance Characteristics





Item	Performance Characteristics
Rated Voltage	250 VAC 320 VAC (IEC60664 -1)
Withstanding Voltage	2,400 VAC (2 seconds, between lines)
Insulation Resistance	> 100 MΩ at 500 VDC (between lines)
Rated Current Range	0.4 – 3.0 A
Rated Inductance Range	0.6 – 62.0 mH minimum
Inductance Measurement Condition	10 kHz
Thermal Class	E (120°C) (R Type) and B (130°C)
Operating Temperature Range	-40°C to +120°C (include self temperature rise) (R Type) and -40°C to +130°C (include self temperature rise)

Table 1 – Ratings & Part Number Reference





Part Number	Rated Current (A)	Inductance (Common) (mH) Minimum	Inductance (Normal) (μH) Typical	DC Resistance/ Line (Ω) Maximum	Temperature Rise (K) Maximum	Marking	Weight (g) Approximate
SSHB10HS-04265	0.4	26.5	949	2.45	50	04 Lot No.	10
SSHB10HS-05177	0.5	17.7	615	1.55	50	05 Lot No.	10
SSHB10HS-06140	0.6	14.0	484	1.17	50	06 Lot No.	10
SSHB10HS-07099	0.7	9.9	339	0.81	50	07 Lot No.	10
SSHB10HS-08068	0.8	6.8	231	0.58	50	08 Lot No.	10
SSHB10HS-10051	1.0	5.1	185	0.43	55	10 Lot No.	10
SSHB10HS-11043	1.1	4.3	135	0.35	50	11 Lot No.	10
SSHB10HS-13030	1.3	3.0	100	0.25	50	13 Lot No.	10
SSHB10HS-17019	1.7	1.9	64	0.17	50	17 Lot No.	10
SSHB10HS-22011	2.2	1.1	41	0.11	55	22 Lot No.	10
SSHB10HS-30006	3.0	0.6	23	0.06	60	30 Lot No.	10
SSHB10HS-R04620	0.4	62.0	949	2.45	50	R04 Lot No.	10
SSHB10HS-R05415	0.5	41.5	615	1.55	50	R05 Lot No.	10
SSHB10HS-R06330	0.6	33.0	484	1.17	50	R06 Lot No.	10
SSHB10HS-R07230	0.7	23.0	339	0.81	50	R07 Lot No.	10
SSHB10HS-R08160	0.8	16.0	231	0.58	50	R08 Lot No.	10
SSHB10HS-R10122	1.0	12.2	185	0.43	55	R10 Lot No.	10
SSHB10HS-R11100	1.1	10.0	135	0.35	50	R11 Lot No.	10
SSHB10HS-R13071	1.3	7.1	100	0.25	50	R13 Lot No.	10
SSHB10HS-R17046	1.7	4.6	64	0.17	50	R17 Lot No.	10
SSHB10HS-R22027	2.2	2.7	41	0.11	55	R22 Lot No.	10
SSHB10HS-R30015	3.0	1.5	23	0.06	60	R30 Lot No.	10

Frequency Characteristics

Common mode







Normal mode







Frequency Characteristics cont.

Common mode







Normal mode







Frequency Characteristics cont.

Common mode







Normal mode







Frequency Characteristics cont.

Common mode







Normal mode







Frequency Characteristics cont.

Common mode





Normal mode





Frequency Characteristics cont.

Common mode



Normal mode



Packaging

Type	Packaging Type	Pieces Per Box
SSHB10HS	Tray	300

Handling Precautions

Precautions for product storage

AC Line Filters should be stored in normal working environments. While the chokes themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage.

KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 70% relative humidity. Atmospheres should be free of chlorine and sulfur bearing compounds. Temperature fluctuations should be minimized to avoid condensation on the parts. Avoid storage near strong magnetic fields, as this might magnetize the product.

For optimized solderability, AC line filters stock should be used promptly and preferably within 6 months of receipt.

Product temperature rise values

The values listed for temperature rise are the result of self-heating in wires when the rated current (commercial frequency) is applied.

When using the product, check and evaluate the value of the core temperature rise under actual operating conditions.

KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

When providing KEMET products and technologies contained herein to other countries, the customer must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the International Traffic in Arms Regulations (ITAR), the US Export Administration Regulations (EAR) and the Japan Foreign Exchange and Foreign Trade Act.

KEMET is a registered trademark of KEMET Electronics Corporation.