



Part Number : [845860017](#)

Product Description : Micro-Change (M12) Tee, 5 Pole, Two Female, One Male, meets NMEA 2000

Series Number : 84586

Status : Active

Product Category : Industrial Tees and Splitters

Engineering Part Number : NMEA-MICT555



Documents and Resources

Drawings

[845860017_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	84586
Description	Micro-Change (M12) Tee, 5 Pole, Two Female, One Male, meets NMEA 2000
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Drop Tee
UPC	822350898270

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	N/A

Physical

Color - Cable Jacket	Gray
Drop Connector	Micro-Change (M12)
Drop Gender	Female
Keyway	Single
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A

Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Net Weight	266.000/g
Poles	5
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Male
Temperature Range - Operating	0°C to +60°C

This document was generated on Dec 21, 2025