Part Number : 2119370002
Product Description : PowerWize 6.00mm, 2-circuit, Screw Mount, Mechanical Keying Option A, Color Coded Red, Vertical Header, Tray
Series Number : 211937
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

2119370002_sd.pdf

2119370001-PK-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

2119410000-AS-000.pdf

2119410000-PS-000.pdf

2119410000-TS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	211937
Description	PowerWize 6.00mm, 2-circuit, Screw Mount, Mechanical Keying Option A, Color Coded Red, Vertical Header, Tray
Application	Wire-to-Board, Wire-to-Busbar
Component Type	PCB Header
Product Name	PowerWize
UPC	193264140541

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	120.0A
Voltage - Maximum	300V

Downloaded from Arrow.com.

Physical

Breakaway	No
Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Red
Diameter	6.00mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Gender	Male
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	42.935/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
Pitch - Mating Interface	19.06mm
Pitch - Termination Interface	19.06mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Screw Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
PowerWize 6.00mm, 2-circuit, Mechanical Keying Option A, Color Coded Red, Receptacle Housing, Bag	2119420002

Downloaded from Arrow.com.

Downloaded from Arrow.com.