

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -
© COPYRIGHT copyright_date BY - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	14JAN2016	J.Z	S.W
	A1	UPDATE TERMINAL INFORMATION	12APR2016	T.D	S.W
	B	ECR-16-005483	10APR2017	T.D	I.Y

A-A








1:1



1:1







Notes

1 PACKAGING: POSITION WAY IN CARDBOX

2 SUITABLE RECEPTALCE CONNECTOR SEE DRAWING: 2298566

3 SUITABLE RETAINER P/N; 2298573-1,2298574-1

4 SUITABLE CONTACTS:SEE TABLE

5 DELIVERY CONDITION:
SLIDER (4) IN END POSITION

6 MOUNTING CONDITION
SLIDER (4) IN PRELOCK POSITION

7 FREE SAPACER FOR HARNESS CONNECTOR MOUNTING

CONTACT 4	PART NO.	WIRE ARANGE	WIRE TYPE
MQS 0.64 LL	5/0-928999-1	0.25~0.35	FLR
	5/0-963715-1	0.5~0.75	
MCON 1.2 CB	1670144-1	0.5~0.75	FLR
	2296537-2		
	1452503-1	1.0~1.5	
	2296537-3		
MCP 2.8K	1241388-1	0.5~1.0	FLR
	1241390-1	1.0~2.5	

ASSY-PART-NO	CODE	COLOR	MATERIAL	REV	DESCRIPTION	ITEM
2298567-2	B	BLACK	PBT	A	SLIDER	4
		NATURAL	MVQ	A	RADIAL SEALING	3
		GREEN	PBT	A	22POSN.,CAVITY BLOCK	2
		BLACK	PBT	A	22PSON.,PLUG HSG.	5
2298567-1	A	BLACK	PBT	A	SLIDER	4
		NATURAL	MVQ	A	RADIAL SEALING	3
		BLACK	PBT	A	22POSN.,CAVITY BLOCK	2
		BLACK	PBT	B	22PSON.,PLUG HSG.	1

TOLERANCES UNLESS OTHERWISE SPECIFIED ACC. TO DIN 16901-140 CONCENTRIC TO NOMINAL DIMENSION. EDITION 1982-11 SHALL APPLY.
Freimasstoleranzen nach DIN 16901-140. Es gilt die Ausgabe 1982-11.

PRODUCT CHARACTERISTICS ACC. QMP EMEA_12
BESONDERE MERKMALE NACH QMP EMEA_12

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J.ZONG 14 JAN2016
CHK S.W ANG 14 JAN2016
APVD -
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

DIMENSIONS: mm
TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
MATERIAL SEE TABLE -
FINISH -

TE Connectivity

NAME 22POSN.,PLUG SIDE, HSG ASSY
MCP 2.8K, MCON1.2CB, MQS 0.64
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2298567	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV B

1471-9 (3/13)

Downloaded from Arrow.com.