

10A, 45V - 200V Schottky Barrier Rectifier

FEATURES

- Low power loss, high efficiency
- Guard ring for overvoltage protection
- High surge current capability
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS


- Switching mode power supply (SMPS)
- Adapters
- DC to DC converters

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I_F	10	A
V_{RRM}	45 - 200	V
I_{FSM}	120	A
$T_{J MAX}$	150	°C
Package	ITO-220AB	
Configuration	Dual dies	




MECHANICAL DATA

- Case: ITO-220AB
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Mounting torque: 0.56 N·m maximum
- Meet JESD 201 class 1A whisker test
- Polarity: As marked
- Weight: 1.70g (approximately)



ITO-220AB



ABSOLUTE MAXIMUM RATINGS (T _A = 25°C unless otherwise noted)							
PARAMETER	SYMBOL	MBRF 1045 CT-Y	MBRF 1060 CT-Y	MBRF 10100 CT-Y	MBRF 10150 CT-Y	MBRF 10200 CT-Y	UNIT
Marking code on the device		MBRF 1045CT	MBRF 1060CT	MBRF 10100CT	MBRF 10150CT	MBRF 10200CT	
Repetitive peak reverse voltage	V_{RRM}	45	60	100	150	200	V
Reverse voltage, total rms value	$V_{R(RMS)}$	31	42	70	105	140	V
Forward current	I_F	10					A
Surge peak forward current, 8.3ms single half sine wave superimposed on rated load	I_{FSM}	120					A
Peak repetitive reverse surge current ⁽¹⁾	I_{RRM}	0.5					A
Peak repetitive forward current (Rated V_R , Square wave, 20KHz)	I_{FRM}	10					A
Critical rate of rise of off-state voltage	dv/dt	10,000					V/μs
Junction temperature	T_J	-55 to +150					°C
Storage temperature	T_{STG}	-55 to +150					°C

Notes:

1. $t_p = 2.0\mu s$, 1.0KHz

THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-case thermal resistance	$R_{\Theta JC}$	3.5	°C/W

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ C$ unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT		
Forward voltage per diode ⁽¹⁾	MBRF1045CT-Y MBRF1060CT-Y MBRF10100CT-Y MBRF10150CT-Y MBRF10200CT-Y	$I_F = 5A, T_J = 25^\circ C$	V_F	-	0.70	V	
				-	0.80	V	
				-	0.85	V	
				-	0.88	V	
	MBRF1045CT-Y MBRF1060CT-Y MBRF10100CT-Y MBRF10150CT-Y MBRF10200CT-Y	$I_F = 10A, T_J = 25^\circ C$		-	0.80	V	
				-	0.90	V	
				-	0.95	V	
				-	0.98	V	
	MBRF1045CT-Y MBRF1060CT-Y MBRF10100CT-Y MBRF10150CT-Y MBRF10200CT-Y	$I_F = 5A, T_J = 125^\circ C$		-	0.57	V	
				-	0.65	V	
				-	0.75	V	
				-	0.78	V	
	MBRF1045CT-Y MBRF1060CT-Y MBRF10100CT-Y MBRF10150CT-Y MBRF10200CT-Y	$I_F = 10A, T_J = 125^\circ C$		-	0.67	V	
				-	0.75	V	
				-	0.85	V	
				-	0.88	V	
Reverse current @ rated V_R per diode ⁽²⁾	MBRF1045CT-Y MBRF1060CT-Y MBRF10100CT-T MBRF10150CT-Y MBRF10200CT-Y	$T_J = 25^\circ C$	I_R	-	100	μA	
				-	15	mA	
	MBRF1045CT-Y MBRF1060CT-Y MBRF10100CT-Y MBRF10150CT-Y MBRF10200CT-Y	$T_J = 125^\circ C$		-	10	mA	
				-	5	mA	

Notes:






1. Pulse test with PW = 0.3ms
2. Pulse test with PW = 30ms


ORDERING INFORMATION


ORDERING CODE ⁽¹⁾	PACKAGE	PACKING
MBRF10xCT-Y	ITO-220AB	50 / Tube

Notes:

1. "x" defines voltage from 45V(MBRF1045CT-Y) to 200V(MBRF10200CT-Y)

CHARACTERISTICS CURVES
 $(T_A = 25^\circ\text{C} \text{ unless otherwise noted})$
Fig.1 Forward Current Derating Curve

Fig.2 Typical Junction Capacitance

Fig.3 Typical Reverse Characteristics

Fig.4 Typical Forward Characteristics

Fig.5 Maximum Non-Repetitive Forward Surge Current


CHARACTERISTICS CURVES $(T_A = 25^\circ\text{C}$ unless otherwise noted)**Fig.6 Typical Transient Thermal Impedance**

PACKAGE OUTLINE DIMENSIONS
ITO-220AB


DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	4.30	4.70	0.169	0.185
A2	2.30	2.96	0.091	0.117
b	0.50	0.90	0.020	0.035
b1	-	1.80	-	0.071
b2	0.95	1.45	0.037	0.057
c	0.46	0.76	0.018	0.030
c2	2.50	3.16	0.098	0.124
D	14.80	15.50	0.583	0.610
D1	2.40	3.20	0.094	0.126
D2	6.30	6.90	0.248	0.272
E	9.60	10.30	0.378	0.406
e	2.41	2.67	0.095	0.105
L	12.60	13.80	0.496	0.543
L4	-	4.10	-	0.161
P	3.00	3.40	0.118	0.134

MARKING DIAGRAM


P/N = Marking Code
 G = Green Compound
 YWW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.