

Shrink sleeve - WMS-2 HF 6,4 (EX10)RL - 0803905

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Shrink sleeve, Roll, white, unlabeled, can be labeled with: THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, THERMOMARK W, Cut, Mounting type: slide on, Cable diameter: 3.2-6.4 mm, Lettering field: 10 x 100000 mm


The figure shows a similar product

Why buy this product

- ✓ WMS ... shrink sleeves provide permanent and captive conductor and cable marking
- ✓ The sleeves are pre-assembled for optimum use of material
- ✓ The sleeves remain flexible after shrinking
- ✓ The conductor to be marked is simply threaded through the sleeve and fixed by shrinking the sleeve
- ✓ The shrink sleeves provide additional electrical insulation and mechanical protection for the conductors
- ✓ Up to four markers per sleeve are separated by perforations

RoHS

Key Commercial Data

Packing unit	1
GTIN	 4 055626 225371
GTIN	4055626225371
Custom tariff number	39173200

Technical data

Dimensions

Length (b)	100 m
Width (a)	10 mm
Cable diameter	3.2 mm ... 6.4 mm

Ambient conditions

Ambient temperature (operation)	-30 °C ... 105 °C
---------------------------------	-------------------

Shrink sleeve - WMS-2 HF 6,4 (EX10)RL - 0803905

Technical data

Ambient conditions

Recommended storage conditions	23°C/50% relative humidity. Storage in a dry and dark place in the original packaging is recommended.
--------------------------------	---

General

Color	white
Base element material	polyolefine
Components	Halogen-free
Material	Polyolefine
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
RoHS compliant	Yes
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5146723 THERMOMARK ROLL X1
	5146231 THERMOMARK X1.2
	5146147 THERMOMARK W2
Ink ribbon	5148007 THERMOMARK-RIBBON 110-WMTB HF
	0801358 THERMOMARK-RIBBON 110-WMSU
	0801360 THERMOMARK-RIBBON 64-WMSU
	0803390 THERMOMARK-RIBBON 25-WMSU
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Marking mounting type	slide on

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------