OMRON Industrial Automation



E2E-X8B1T18-M1

Proximity sensor, inductive, nickel-brass, short body, M18, shielded, 8 mm, DC, 3-wire, PNP NO, IO-Link COM3, M12 connector

Downloaded from Arrow.com.

Specifications

Size	M18
Mounting type	Quasi-flush
Sensing distance	8 mm
Overall length of sensor	53 mm
Thread length	34 mm
Material housing	Brass, nickel plated
Output type	IO-Link, PNP
Operation mode	NO
Connection method	Connector M12
Cable specifications	-
IO-Link function	✔
IO-Link baud rate	COM3 (230.4 kbps)
Degree of protection (IP)	IP67/IP69K

Accessories



Y92E-J18S30 OMS Mounting Sleeves e-jig for M18 Prox

Downloaded from Arrow.com.

Related products




M12 Connectors & Cordsets
Industrial connectors & cordsets for any application

Downloads

CAD Library



E2E NEXT
Datasheet
EN PDF 40 MB



E2E(Q) - Basic Models
Index list
EN PDF 7.27 MB



E2E(Q) - Premium Models
Index list
EN PDF 719 KB



E2E(Q)-XB_XC_basic_model
Instruction Sheet
EN PDF 2.28 MB



E2E[Q]-XxBxxxx
IO-Link IODD file
EN ZIP 1.35 MB



IO-Link Series
Brochure
EN PDF 7.95 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 10 September, 2026. Click here for terms of use.

Downloaded from Arrow.com.