Part Number : 550912074
Product Description : SlimStack Board-to-Board Connector, 0.635mm Pitch, 0.635 Series, Plug, 6.00 or 12.00mm Mated Height, 6.40mm Mated Width, 200 Circuits, with Embossed Tape on Reel Packaging
Series Number : 55091
Status : Active
Product Category : Board-to-Board Connectors



Documents and Resources

Drawings

550912074_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

550919200-200.pdf

527600000-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33; 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Series	0.635, Rigid
Description	SlimStack Board-to-Board Connector, 0.635mm Pitch, 0.635 Series, Plug, 6.00 or 12.00mm Mated Height, 6.40mm Mated Width, 200 Circuits, with Embossed Tape on Reel Packaging
Application	Board-to-Board, Signal
Comments	Stacking-Type
Component Type	Plug
Product Name	SlimStack
UPC	191128871525

Agency

UL	E29179

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	100V

Downloaded from Arrow.com.

Physical

Breakaway	No
Circuits (Loaded)	200
Circuits (maximum)	200
Color - Resin	Black
Durability (mating cycles max)	50
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Mated Height	12.00mm, 6.00mm
Mated Width	6.40mm
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1562.609/mg
Number of Rows	2
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
Pitch - Mating Interface	0.635mm
Polarized to PCB	Yes
Robotic Placement	Metal Cap
Shrouded	Shrouded
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
0.635mm Pitch Vertical SlimStack	52885

Downloaded from Arrow.com.

Receptacles	
0.635mm Pitch Vertical SlimStack Receptacles	52901

Downloaded from Arrow.com.