

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	-	-	-	-






2*2P～2*4P


NOTES:
1.CURRENT RATING: 2.0AMP
2.CONTACT RESISTANCE: 20mΩ MAX
3.WITHSTAND VOLTAGE: 500V AC/DC
4.INSULATION RESISTANCE: 1000MΩ MIN
5.OPERATION TEMPERATURE: -40℃ TO +105℃
6.CONTACT MATERIAL:COPPER ALLOY
7.CONTACT PLATING:
10u''AU ON CONTACT AREA OVER NI UNDERPLATING
GOLDFLASH ON SOLDERING AREA OVER NI UNDERPLATING
8.INSULATOR MATERIAL:PA9T UL94V-O
9.RECOMMENDED SOLDERING PROCESS: REFLOW
PEAK TEMPERATURE: 260℃,5S



SECTION A-A



SECTION B-B



RECOMMENDED P.C.B LAYOUT
(COMPONENT SIDE)

		40	4-2271597-0
		20	2-2271597-0
		8	2271597-8
		6	2271597-6
		4	2271597-4
TAPE REEL+CAP	PA9T UL94V-0	2	2271597-2
PACKAGING	INSULATOR	POS	PN

PRODUCT FAMILY TABLE

2271597

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± 0.30
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL -
FINISH -

DWN BO GAO 27APR2015
CHK KOBBY ZHAO -
APVD XIANG XU -
PRODUCT SPEC 108-137777
APPLICATION SPEC -
WEIGHT 0.000000

TE Connectivity

NAME AMPMODU, REC HDR, 2.00PITCH DOUBLE ROW, SMT, 3.56H -

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2271597	-

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV C

1471-9 (1/15)

Downloaded from Arrow.com.