




Part Number : [557551519](#)
Product Description : 2.00mm Pitch MicroTPA Wire-to-Board Header, Vertical, Shrouded, Kinked PC Tail, with Inner Positive Lock, 15 Circuits
Series Number : 55755
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings
[557551519_sd.pdf](#)

3D Models and Design Files
[557551519_stp.zip](#)

Specifications
[SPK-55755-001-001.pdf](#)
[PS-51216-007-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	55755
Description	2.00mm Pitch MicroTPA Wire-to-Board Header, Vertical, Shrouded, Kinked PC Tail, with Inner Positive Lock, 15 Circuits
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Name	MicroTPA
UPC	822348802463

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	250V

Physical

Breakaway	No
Circuits (Loaded)	15
Circuits (maximum)	15
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No

Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	13.45mm
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1251.000/mg
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PC Tail Length	3.30mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.00mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
MicroTPA Receptacle Housings	<u>51216</u>

This document was generated on Mar 14, 2025