

CUSTOMER PRINT



PART NUMBER: CA6280XSPXXX90

- NOTES:
- 1. FINISHED PRODUCT TO BE COILED
 - 2. OVERMOLD BOOT MATERIAL: UV PBT, BLACK
 - 2. ELECTRICAL TEST: 100% CONTINUITY
 - 4. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE

ASS'Y P/N	NO. OF CONTACTS
CA62802SPXXX90	2
CA62803SPXXX90	3
CA62804SPXXX90	4
CA62805SPXXX90	5
CA62806SPXXX90	6
CA62807SPXXX90	7
CA62808SPXXX90	8
CA6280XSPXXX90	

ASS'Y P/N	"X" DIM
CA6280XSP03990	3 FT. 3 1/2 IN. ±2 IN. [1M ±50.8mm]
CA6280XSP07990	6 FT. 7 IN. ±2 IN. [2M ±50.8mm]
CA6280XSP19790	16 FT. 5 IN. ±4 IN. [5M ±101.6mm]
CA6280XSP39490	32 FT. 9 3/4 IN. ±8 IN. [10M ±203.2mm]
CA6280XSPXXX90	

CABLE LENGTH IN "INCHES"
NO. OF CONTACTS



ASSY P/N	CABLE	COLOR CODE END "A"							
CA62802SPXXX90	2/20 AWG O.D. 0.215 REF	COLOR CODE							
		POS. 1	POS. 2						
CA62803SPXXX90	3/20 AWG O.D. 0.220 REF	WIRE COLOR CODE							
		POS. 1	POS. 2	POS. 3					
		BLK	WHT	GRN					
CA62804SPXXX90	4/20 AWG O.D. 0.235 REF	WIRE COLOR CODE							
		POS. 1	POS. 2	POS. 3	POS. 4				
		BLK	WHT	GRN	RED				
CA62805SPXXX90	5/20 AWG O.D. 0.255 REF	WIRE COLOR CODE							
		POS. 1	POS. 2	POS. 3	POS. 4	POS. 5			
		BLK	WHT	GRN	RED	BLU			
CA62806SPXXX90	6/20 AWG O.D. 0.275 REF	WIRE COLOR CODE							
		POS. 1	POS. 2	POS. 3	POS. 4	POS. 5	POS. 6		
		BLK	WHT	GRN	RED	BLU	VIO		
CA62807SPXXX90	8/20 AWG O.D. 0.300 REF	WIRE COLOR CODE							
		POS. 1	POS. 2	POS. 3	POS. 4	POS. 5	POS. 6	POS. 7	
		BLK	WHT	GRN	RED	BLU	VIO	GRY	
CA62808SPXXX90	8/20 AWG O.D. 0.300 REF	WIRE COLOR CODE							
		POS. 1	POS. 2	POS. 3	POS. 4	POS. 5	POS. 6	POS. 7	POS. 8
		BLK	WHT	GRN	RED	BLU	VIO	GRY	BRN

DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS UNLESS INDICATED

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

RoHS COMPLIANT

A	MA	06-04-21	DRAWING CREATED PER DOR 21-109359DS											
REV.	INIT.	DATE	DESCRIPTION											
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			ORIG. DRAWN BY: MA				DATE: 06-04-21				 601 E. WILDWOOD VILLA PARK, IL 60181			
			CHECKED BY:											
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			APPROVED BY:				TITLE: CABLE ASSEMBLY (2-8) #20 SOCKET CONTACTS INSTA-CLICK™ MINI-CON-X STANDARD PRODUCT				CUSTOMER:			
			SCALE		SIZE								SHEET	
			NTS		B								1 OF 1	
▷ = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX			FILE:		DIRECTORY:		PART NUMBER:		CA6280XSPXXX90					
			CA6280XSPXXX90		SLW									
			REV A											