

DESCRIPTION

The LX5530 is a power amplifier optimized for the FCC Unlicensed National Information Infrastructure (U-NII) band, HyperLAN2 and Japan WLAN applications in the 4.9 – 5.9 GHz frequency range. The PA is implemented as a three-stage monolithic microwave integrated circuit (MMIC) with active bias, on-chip input matching and output pre-matching. The device is manufactured with an InGaP/GaAs Heterojunction Bipolar Transistor (HBT) IC process (MOCVD). It operates with a single positive voltage supply of 3 – 5V, with high power gain of up to 33dB. When operated at 5V supply voltage, it provides up to +25dBm linear output power for 802.11a OFDM spectrum mask compliance, and low EVM of 3% for up to +23dBm output power in the 4.9-5.9GHz band.


The LX5530 also features an on-chip power detector at the output port of the PA to help reduce BOM cost and PCB space for implementation of power control in a typical wireless system. The power detector is integrated with a temperature-compensated bias network and provides very stable response across a wide range of output power levels, over temperature extremes from -40 to +85°C.

The LX5530 is available in a 16-pin 3mmx3mm micro-lead package (MLP). The compact footprint, low profile, and excellent thermal capability makes the LX5530 an ideal solution for broadband, high-gain power amplifier requirements for IEEE 802.11a, and Hiperlan2 portable WLAN, as well as the emerging 802.16 WiMAX applications.


IMPORTANT: For the most current data, consult MICROSEMI's website: <http://www.microsemi.com>

KEY FEATURES

- Broadband 4.9 – 5.9GHz Operation
- Advanced InGaP HBT
- Single-Polarity 3 – 5V Supply
- Power Gain up to ~ 33dB for $V_C=5V$, $I_{CQ} = 250mA$
- Power Gain > ~28dB across 4.9-5.85GHz
- OFDM Mask Compliance Power $P_{out} \sim +25dBm$ over 4.9-5.85GHz (ACPR ~ -50dBc @ $\pm 30MHz$ Offset)
- P_{out} up to +23dBm with EVM ~3% ($V_C = 5V$)
- EVM < ~2.5% for $P_{out}=+21dBm$ across 4.9-5.85GHz ($V_C = 5V$)
- EVM < ~2.5% for $P_{out}=+19dBm$ across 4.9-5.85GHz ($V_C = 4V$)
- Total Current ~250mA for $P_{out} = +20dBm$, Duty Cycle = 99% ($V_C = 4V$)
- Complete On-Chip Input Match
- Simple Output Match for Optimal Broadband EVM
- On-Chip RF Decoupling
- Temperature-Compensated On-Chip Output Power Detector with Wide Dynamic Range
- Small Footprint: 3x3mm
- Low Profile: 0.9mm

BLOCK DIAGRAM

APPLICATIONS

- FCC U-NII Wireless
- IEEE 802.11a
- HyperLAN2
- 5GHz Cordless Phone
- IEEE 802.16 WiMAX

3X3MM MLP PACKAGE

PACKAGE ORDER INFO

LQ	Plastic MLPQ
	16 pin
	RoHS Compliant / Pb-free
	LX5530LQ

Note: Available in Tape & Reel. Append the letters "TR" to the part number. (i.e. LX5530LQ-TR)



Microsemi

INFORMATION

Thank you for your interest in Microsemi® IPG products.

The full data sheet for this device contains proprietary information.

To obtain a copy, please contact your local Microsemi sales representative. The name of your local representative can be obtained at the following link

<http://www.microsemi.com/contact/contactfind.asp>

or

Contact us directly by sending an email to:

IPGdatasheets@microsemi.com

Be sure to specify the data sheet you are requesting and include your company name and contact information and or vcard.

We look forward to hearing from you.