




9	FERRULE	COPPER	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1		DRAWN	M.ZHANG	07/24/10						
7	HUT HEX	BRASS	NICKEL	1		CHECKED								
6	LOCK WASHER	BRASS	NICKEL	1		ISSUED			PART DESCRIPTION TNC BULKHEAD CRIMP JACK – 50 OHM (FOR RG–58C/U CABLE)					
5	GASKET	RUBBER	RED	1		SHEET	1 OF 1							
4	BARREL	BRASS	NICKEL	1					PART NO. 122168					
3	INSULATOR	PTFE	NATURAL	1										
2	BODY	BRASS	NICKEL	1					DWG. NO. 122168.DWG					
1	HOUSING	BRASS	NICKEL	1										
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE C:/CONNEX/122168.DWG			REV.	NC	SIZE	A	SCALE	NA