

MD and MDP Series



MD (Soft Actuator) MDP (Hard Actuator)

Features/Benefits

- Short travel
- Good tactile feedback
- Self cleaning
- ROHS
- 2 actuator material

Typical Applications

- Aircraft
- Instrument
- Panels
- Radio equipment

Specification

Function : Momentary action
 Contact type : Normally Open - SPST
 Terminals : Through hole PCB terminations

Mechanical

	Operating force (N)	Tactile feeling (Δ%)	Operating life	Travel (mm)
MD	2,4 N ± 25%	≥ 15%	≥ 10 ⁶	0.95 mm ± 0.35
MDP	2,6 N ± 25%	≥ 25%	≥ 2x10 ⁵	0.4 mm ± 0.25

Electrical



	Silver	Gold
Maximum power:	1,0 VA	0,2 VA
Maximum voltage:	100 Vdc	100 Vdc
Minimum voltage:	20 mVdc	20 mVdc
Min/max current:	1.0 mA – 100 mA	50 µA – 50 mA
Dielectric strength:	≥ 250 Vrms	
Contact resistance:	≤ 100 mΩ	
Insulation resistance:	Initial measurement: ≥ 1 GΩ	
(between terminals)	After damp heat : ≥ 10 MΩ	
Bounce time:	≤ 3ms	

Environmental

	Silver	Gold
Operating temperature	- 25°C / + 70°C	- 55°C / + 85°C

Part Number Description


For any part number different from those listed below, please consult your local representative




Dimensions shown in mm (inch)
 Specifications and dimensions subject to change

www.ckswitches.com

MD



MDP



Bouton MDP

