62 mm C-Series module with TRENCHSTOP™IGBT7 and emitter controlled 7 diode and pre-applied thermal interface material



Features

- Electrical features
  - V_{CES} = 1200 V
  - $I_{C\ nom}$ = 450 A / I_{CRM} = 900 A
  - TRENCHSTOP™ IGBT7
  - $V_{CE,sat}$ with positive temperature coefficient
  - Suitable Infineon gate drivers can be found under https://www.infineon.com/gdfinder
- Mechanical features
  - 4 kV AC 1 min insulation
  - High creepage and clearance distances
  - High power density
  - Isolated base plate
  - Package with CTI > 400
  - Standard housing
  - Pre-applied thermal interface material


Potential applications

- Servo drives
- Solar applications
- UPS systems
- Motor drives
- High-power converters
- Commercial agriculture vehicles
- Three-level applications

Product validation

- Qualified for industrial applications according to the relevant tests of IEC 60747, 60749 and 60068

Description



Downloaded from Arrow.com.

Table of contents

Description . . . 1
Features . . . 1
Potential applications . . . 1
Product validation . . . 1
Table of contents . . . 2
1 Package . . . 3
2 IGBT, T1 / T2 . . . 3
3 Diode, D1 / D2 . . . 5
4 Characteristics diagrams . . . 7
5 Circuit diagram . . . 11
6 Package outlines . . . 12
7 Module label code . . . 13
Revision history . . . 14
Disclaimer . . . 15

Downloaded from Arrow.com.

1 Package

Table 1 Insulation coordination

Parameter	Symbol	Note or test condition	Values	Unit
Isolation test voltage	V_{ISOL}	RMS, f = 50 Hz, *t* = 60 s	4.0	kV
Material of module baseplate			Cu	
Internal isolation		basic insulation (class 1, IEC 61140)	Al_2O_3	
Creepage distance	d_{Creep}	terminal to heatsink	29.0	mm
Creepage distance	d_{Creep}	terminal to terminal	23.0	mm
Clearance	d_{Clear}	terminal to heatsink	23.0	mm
Clearance	d_{Clear}	terminal to terminal	11.0	mm
Comparative tracking index	*CTI*		> 400	
Relative thermal index (electrical)	*RTI*	housing	140	°C

Table 2 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Stray inductance module	L_{sCE}				20		nH
Module lead resistance, terminals - chip	$R_{CC'+EE'}$	T_H = 25 °C, per switch			0.5		mΩ
Storage temperature	T_{stg}			-40		125	°C
Maximum baseplate operation temperature	T_{BPmax}					125	°C
Mounting torque for module mounting	*M*	- Mounting according to valid application note	M5, Screw	3		6	Nm
Terminal connection torque	*M*	- Mounting according to valid application note	M6, Screw	2.5		5	Nm
Weight	*G*				340		g

Note: Storage and shipment of modules with TIM => see AN2012-07

2 IGBT, T1 / T2

Table 3 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CES}		T_{vj} = 25 °C	1200	V

(table continues...)

Downloaded from Arrow.com.

Table 3 (continued) Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Continuous DC collector current	I_{CDC}	$T_{vj\,max}$ = 175 °C	T_H = 50 °C	450	A
Maximum RMS module DC-terminal current	I_{tRMS}		$T_{Terminal}$ = 115 °C, T_C = 90 °C	650	A
			$T_{Terminal}$ = 115 °C, T_C = 115 °C	600	
Repetitive peak collector current	I_{CRM}	t_p limited by $T_{vj\,op}$		900	A
Gate-emitter peak voltage	V_{GES}			±20	V

Table 4 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter saturation voltage	$V_{CE\,sat}$	I_C = 450 A, V_{GE} = 15 V	T_{vj} = 25 °C		1.50	1.75	V
			T_{vj} = 125 °C		1.65		
			T_{vj} = 150 °C		1.70		
			T_{vj} = 175 °C		1.75		
Gate threshold voltage	V_{GEth}	I_C = 9 mA, V_{CE} = V_{GE}, T_{vj} = 25 °C		5.15	5.80	6.45	V
Gate charge	Q_G	V_{GE} = ±15 V, V_{CC} = 600 V			7.41		µC
Internal gate resistor	R_{Gint}	T_{vj} = 25 °C			0.7		Ω
Input capacitance	C_{ies}	f = 100 kHz, T_{vj} = 25 °C, V_{CE} = 25 V, V_{GE} = 0 V			70.8		nF
Reverse transfer capacitance	C_{res}	f = 100 kHz, T_{vj} = 25 °C, V_{CE} = 25 V, V_{GE} = 0 V			0.354		nF
Collector-emitter cut-off current	I_{CES}	V_{CE} = 1200 V, V_{GE} = 0 V	T_{vj} = 25 °C			0.1	mA
Gate-emitter leakage current	I_{GES}	V_{CE} = 0 V, V_{GE} = 20 V, T_{vj} = 25 °C				100	nA
Turn-on delay time (inductive load)	t_{don}	I_C = 450 A, V_{CC} = 600 V, V_{GE} = ±15 V, R_{Gon} = 0.51 Ω	T_{vj} = 25 °C		0.370		µs
			T_{vj} = 125 °C		0.381		
			T_{vj} = 150 °C		0.385		
			T_{vj} = 175 °C		0.389		
Rise time (inductive load)	t_r	I_C = 450 A, V_{CC} = 600 V, V_{GE} = ±15 V, R_{Gon} = 0.51 Ω	T_{vj} = 25 °C		0.043		µs
			T_{vj} = 125 °C		0.049		
			T_{vj} = 150 °C		0.051		
			T_{vj} = 175 °C		0.052		

(table continues...)

Downloaded from Arrow.com.

Table 4 (continued) Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Turn-off delay time (inductive load)	t_{doff}	I_C = 450 A, V_{CC} = 600 V, V_{GE} = ±15 V, R_{Goff} = 1.5 Ω	T_{vj} = 25 °C		0.522		µs
			T_{vj} = 125 °C		0.588		
			T_{vj} = 150 °C		0.610		
			T_{vj} = 175 °C		0.623		
Fall time (inductive load)	t_f	I_C = 450 A, V_{CC} = 600 V, V_{GE} = ±15 V, R_{Goff} = 1.5 Ω	T_{vj} = 25 °C		0.124		µs
			T_{vj} = 125 °C		0.263		
			T_{vj} = 150 °C		0.307		
			T_{vj} = 175 °C		0.351		
Turn-on energy loss per pulse	E_{on}	I_C = 450 A, V_{CC} = 600 V, L_σ = 25 nH, V_{GE} = ±15 V, R_{Gon} = 0.51 Ω, di/dt = 6900 A/µs (T_{vj} = 175 °C)	T_{vj} = 25 °C		14.1		mJ
			T_{vj} = 125 °C		22.2		
			T_{vj} = 150 °C		25		
			T_{vj} = 175 °C		27.7		
Turn-off energy loss per pulse	E_{off}	I_C = 450 A, V_{CC} = 600 V, L_σ = 25 nH, V_{GE} = ±15 V, R_{Goff} = 1.5 Ω, dv/dt = 3100 V/µs (T_{vj} = 175 °C)	T_{vj} = 25 °C		36.9		mJ
			T_{vj} = 125 °C		58.9		
			T_{vj} = 150 °C		65.6		
			T_{vj} = 175 °C		72.2		
SC data	I_{SC}	V_{GE} ≤ 15 V, V_{CC} = 800 V, V_{CEmax}=V_{CES}-L_{sCE}*di/dt	t_P ≤ 8 µs, T_{vj}=150 °C		1700		A
			t_P ≤ 6 µs, T_{vj}=175 °C		1500		
Thermal resistance, junction to heat sink	R_{thJH}	per IGBT, Valid with IFX pre-applied Thermal Interface Material				0.123	K/W
Temperature under switching conditions	$T_{vj\,op}$			-40		175	°C

Note: $T_{vj\,op}$ > 150 °C is only allowed for operation at overload conditions. For detailed specifications please refer to AN 2018-14.

3 Diode, D1 / D2

Table 5 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak reverse voltage	V_{RRM}		T_{vj} = 25 °C	1200	V
Continuous DC forward current	I_F			450	A

(table continues...)

Downloaded from Arrow.com.

Table 5 (continued) Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Repetitive peak forward current	I_{FRM}	t_P = 1 ms		900	A
I^2t - value	I^2t	t_P = 10 ms, V_R = 0 V	T_{vj} = 125 °C	14400	A^2s
			T_{vj} = 175 °C	10400	

Table 6 Characteristic values


Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Forward voltage	V_F	I_F = 450 A, V_{GE} = 0 V	T_{vj} = 25 °C		1.80	2.10	V
			T_{vj} = 125 °C		1.70		
			T_{vj} = 150 °C		1.65		
			T_{vj} = 175 °C		1.60		
Peak reverse recovery current	I_{RM}	V_{CC} = 600 V, I_F = 450 A, V_{GE} = -15 V, -di$_F$/dt = 6900 A/µs (T_{vj} = 175 °C)	T_{vj} = 25 °C		377		A
			T_{vj} = 125 °C		480		
			T_{vj} = 150 °C		509		
			T_{vj} = 175 °C		538		
Recovered charge	Q_r	V_{CC} = 600 V, I_F = 450 A, V_{GE} = -15 V, -di$_F$/dt = 6900 A/µs (T_{vj} = 175 °C)	T_{vj} = 25 °C		39.2		µC
			T_{vj} = 125 °C		65.6		
			T_{vj} = 150 °C		76.4		
			T_{vj} = 175 °C		87.2		
Reverse recovery energy	E_{rec}	V_{CC} = 600 V, I_F = 450 A, V_{GE} = -15 V, -di$_F$/dt = 6900 A/µs (T_{vj} = 175 °C)	T_{vj} = 25 °C		18		mJ
			T_{vj} = 125 °C		32.8		
			T_{vj} = 150 °C		37.4		
			T_{vj} = 175 °C		41.9		
Thermal resistance, junction to heat sink	R_{thJH}	per diode, Valid with IFX pre-applied Thermal Interface Material				0.186	K/W
Temperature under switching conditions	$T_{vj\,op}$			-40		175	°C

Note: $T_{vj\,op}$ > 150 °C is only allowed for operation at overload conditions. For detailed specifications please refer to AN 2018-14.


Downloaded from Arrow.com.

4 Characteristics diagrams


Output characteristic (typical), IGBT, T1 / T2
$I_C = f(V_{CE})$
V_{GE} = 15 V




Output characteristic field (typical), IGBT, T1 / T2
$I_C = f(V_{CE})$
T_{vj} = 175 °C



Transfer characteristic (typical), IGBT, T1 / T2
$I_C = f(V_{GE})$
V_{CE} = 20 V



Gate charge characteristic (typical), IGBT, T1 / T2
$V_{GE} = f(Q_G)$
I_C = 450 A, T_{vj} = 25 °C




Downloaded from Arrow.com.

Capacity characteristic (typical), IGBT, T1 / T2

$C = f(V_{CE})$


$f = 100$ kHz, $V_{GE} = 0$ V, $T_{vj} = 25$ °C



Switching times (typical), IGBT, T1 / T2

$t = f(I_C)$


$R_{Goff} = 1.5\ \Omega$, $R_{Gon} = 0.51\ \Omega$, $V_{CC} = 600$ V, $V_{GE} = \pm 15$ V, $T_{vj} = 175$ °C



Switching times (typical), IGBT, T1 / T2

$t = f(R_G)$


$I_C = 450$ A, $V_{CC} = 600$ V, $V_{GE} = \pm 15$ V, $T_{vj} = 175$ °C



Voltage slope (typical), IGBT, T1 / T2

$dv/dt = f(R_G)$

$I_C = 450$ A, $V_{CC} = 600$ V, $V_{GE} = \pm 15$ V, $T_{vj} = 25$ °C




Downloaded from Arrow.com.

Switching losses (typical), IGBT, T1 / T2

$E = f(I_C)$


$R_{Goff} = 1.5\ \Omega$, $R_{Gon} = 0.51\ \Omega$, $V_{CC} = 600\ V$, $V_{GE} = \pm 15\ V$



Switching losses (typical), IGBT, T1 / T2

$E = f(R_G)$


$I_C = 450\ A$, $V_{CC} = 600\ V$, $V_{GE} = \pm 15\ V$



Reverse bias safe operating area (RBSOA), IGBT, T1 / T2


$I_C = f(V_{CE})$

$R_{Goff} = 1.5\ \Omega$, $V_{GE} = \pm 15\ V$, $T_{vj} = 175\ °C$



Transient thermal impedance, IGBT, T1 / T2


$Z_{th} = f(t)$



Downloaded from Arrow.com.

Forward characteristic (typical), Diode, D1 / D2


$I_F = f(V_F)$



Switching losses (typical), Diode, D1 / D2

$E_{rec} = f(I_F)$


$R_{Gon} = 0.51\ \Omega$, $V_{CE} = 600\ V$



Switching losses (typical), Diode, D1 / D2


$E_{rec} = f(R_G)$

$V_{CE} = 600\ V$, $I_F = 450\ A$



Transient thermal impedance, Diode, D1 / D2

$Z_{th} = f(t)$



Downloaded from Arrow.com.

5 Circuit diagram




Figure 1

Downloaded from Arrow.com.

6 Package outlines




Figure 2

Downloaded from Arrow.com.

7 Module label code

Module label code			
Code format	Data Matrix		Barcode Code128
Encoding	ASCII text		Code Set A
Symbol size	16x16		23 digits
Standard	IEC24720 and IEC16022		IEC8859-1
Code content	*Content* Module serial number Module material number Production order number Date code (production year) Date code (production week)	*Digit* 1 – 5 6 - 11 12 - 19 20 – 21 22 – 23	*Example* 71549 142846 55054991 15 30
Example	71549142846550549911530		71549142846550549911530

Figure 3

Downloaded from Arrow.com.

Revision history

Document revision	Date of release	Description of changes
1.00	2023-07-14	Initial version

Downloaded from Arrow.com.

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2023-07-14

Published by

Infineon Technologies AG

81726 Munich, Germany

© 2023 Infineon Technologies AG

All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ABH331-001

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

Downloaded from Arrow.com.