




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **2.1 – 3.31 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	20.57 mm[.81 in]
Compatible Insulation Diameter Range	2.79 – 4.32 mm[.11 – .17 in]
Terminal Material Thickness	.4 mm[.015 in]
Wire Size	2.1 – 3.31 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	3000
Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2151771-1
OCEAN_2.0_Applicator-S-120F180F-RSM

TE Part # 1494210-1
110 FASTON,TAB,22-17 AWG, JIS C260

TE Part # 60794-2
FASTIN NECESSARY?? - separate GPL: 326

TE Part # 63165-2
FASTON 110 AMPLIVAR TAB 23-19 MAG TPBR

TE Part # 7-2151771-7
OCEAN_2.0_SPARE_PART_KIT-120F180F

TE Part # 180353-2
250 FASTON,TAB,12-10 AWG,TPBR

TE Part # 2151771-2
OCEAN_2.0_Applicator-S-120F180F-RSA

TE Part # 2305570-1
Strip Terminal Cutter-Side Feed-No Crimp


Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(117)

Insertion & Extraction Tools(6)

Insulation Boots & Sleeves(16)



Magnet Wire Terminals(1)



PCB Terminals(131)



Quick Disconnects(411)




Splices(4)


Customers Also Bought



TE Part #2056350005
ES-CAP-NO.3-B8-0-40MM



TE Part #41900
SPLC AMVAR 3000-7000 020TPBR



TE Part #60850-2
187 FASTON TAB 18-14 AWG TPBR



TE Part #60960-3
250 FASTON FLAG REC 12-10 AWG TPBR



TE Part #160913-2
FF 250 REC 2.5-4.0MM2 TPBR



TE Part #1-1355470-5
2POS MQS TAB COD A




TE Part #1742753-1
FASTON 2MM TAB 18-22AWG TPBR



TE Part #1742975-1
110 PL REC. 22-18AWG TPBR



TE Part #2138558-1
2P GENERATION Y Cap, Single-Pi



TE Part #2177610-1
TAB1.2X0.6,TERMINAL,SWS,CB

Documents

Product Drawings

250 FASTON TAB 14-12 AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_61281-3_V.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_61281-3_V.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_61281-3_V.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON TERMINALS \(INSULATED AND UNINSULATED\) - FULL CATALOG](#)

English

[FASTON Tabs](#)

English

Product Specifications

[EB**General Application Specification for Open Barrel Terminals](#)

English

[Application Specification](#)

English

[Application Specification](#)

English

Agency Approvals

[CSA Certificate](#)

English

[CSA Certificate](#)

English