

3050293
<https://www.phoenixcontact.com/us/products/3050293>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fuse modular terminal block, fuse type: Glass / ceramics / ..., fuse type: G / 5 x 20, nom. voltage: 500 V, nominal current: 6.3 A, connection method: Quick connection, 1 level, Rated cross section: 1.5 mm², cross section: 0.5 mm²- 2.5 mm², mounting type: NS 35/7,5, NS 35/15, color: black

Your advantages

- An extremely compact design
- Test pick-off on both sides in the fuse lever
- Tested for railway applications

Commercial data

Item number	3050293
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE03
Product key	BE3134
Catalog page	Page 264 (C-1-2019)
GTIN	4046356056137
Weight per piece (including packing)	17.235 g
Weight per piece (excluding packing)	17.235 g
Customs tariff number	85369095
Country of origin	CN

QTC 2,5-HESI (5X20) - Fuse modular terminal block



3050293

<https://www.phoenixcontact.com/us/products/3050293>

Technical data

Notes

General	The current is determined by the fuse used, the voltage by the light indicator.
---------	---

Product properties

Product type	Fuse terminal block
Area of application	Railway industry
	Machine building
	Plant engineering
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Fuse type	Glass / ceramics / ...
Rated surge voltage	6 kV
Maximum power dissipation for nominal condition	0.77 W
Fuse	G / 5 x 20
Maximum power dissipation	max. 1.6 W (with single arrangement of the fuse terminal block in the event of overload)
	max. 1.6 W (With interconnected arrangement of several fuse terminal blocks in the event of overload)
	max. 4 W (with single arrangement of the fuse terminal block in the event of a short-circuit)
	max. 2.5 W (With interconnected arrangement of several fuse terminal blocks in the event of a short-circuit)

Connection data

Number of connections per level	2
Frequency of connections with the same cross section	100.00
Nominal cross section	2.5 mm²

1 level

Connection in acc. with standard	IEC 60947-7-3
Conductor cross section rigid	0.5 mm² ... 2.5 mm²
Cross section AWG	20 ... 14 (converted acc. to IEC)
Conductor cross section flexible	0.5 mm² ... 2.5 mm²
Conductor cross section, flexible [AWG]	20 ... 14 (converted acc. to IEC)
Nominal current	6.3 A
Maximum load current	6.3 A (the current is determined by the fuse used)

QTC 2,5-HESI (5X20) - Fuse modular terminal block



3050293

<https://www.phoenixcontact.com/us/products/3050293>

Nominal voltage	500 V
Nominal cross section	1.5 mm ²

Dimensions

Width	6.2 mm
End cover width	2.2 mm
Height	82.5 mm
Depth on NS 35/7,5	64.9 mm
Depth on NS 35/15	72.4 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Cable/line

Wire diameter incl. insulation	3.8 mm
--------------------------------	--------

Mechanical properties

Mechanical data

Open side panel	Yes
-----------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

QTC 2,5-HESI (5X20) - Fuse modular terminal block



3050293

<https://www.phoenixcontact.com/us/products/3050293>

Connection in acc. with standard

IEC 60947-7-3

Mounting

Mounting type

NS 35/7,5

NS 35/15

QTC 2,5-HESI (5X20) - Fuse modular terminal block




3050293

<https://www.phoenixcontact.com/us/products/3050293>

Drawings

Application drawing



Fuse terminal blocks in interconnected arrangement,
block consisting of 5 fuse terminal blocks


QTC 2,5-HESI (5X20) - Fuse modular terminal block



3050293

<https://www.phoenixcontact.com/us/products/3050293>

Application drawing



Fuse terminal block in single arrangement,
block consisting of one fuse terminal block and 4 feed-through terminal blocks


QTC 2,5-HESI (5X20) - Fuse modular terminal block

3050293

<https://www.phoenixcontact.com/us/products/3050293>



Circuit diagram



QTC 2,5-HESI (5X20) - Fuse modular terminal block



3050293

<https://www.phoenixcontact.com/us/products/3050293>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3050293>

 CSA Approval ID: 2030668				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Use group B	300 V	10 A	20 - 14	-
Use group C	300 V	10 A	20 - 14	-

 IECEE CB Scheme Approval ID: NL-65057				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	500 V	6.3 A	-	0.5 - 2.5

 EAC Approval ID: RU C-DE.BL08.B.00539				
---	--	--	--	--

 cULus Recognized Approval ID: E60425				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
Use group B	300 V	15 A	20 - 14	-
Use group C	300 V	15 A	20 - 14	-

 KEMA-KEUR Approval ID: 71-113330				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	500 V	6.3 A	-	0.5 - 2.5

 NK Approval ID: 09 ME 139				
---	--	--	--	--

ABS Approval ID: 22-2196825-PDA				
---	--	--	--	--

QTC 2,5-HESI (5X20) - Fuse modular terminal block

3050293

<https://www.phoenixcontact.com/us/products/3050293>



DNV

Approval ID: TAE000014H

QTC 2,5-HESI (5X20) - Fuse modular terminal block



3050293

<https://www.phoenixcontact.com/us/products/3050293>

Classifications

ECLASS

ECLASS-13.0	27250113
-------------	----------

ETIM

ETIM 9.0	EC000899
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

QTC 2,5-HESI (5X20) - Fuse modular terminal block



3050293

<https://www.phoenixcontact.com/us/products/3050293>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com