

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION





COPYRIGHT - By -

ALL RIGHTS RESERVED.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	ECR-14-003969	25MAR16	T.Q	W.H


(AS SHOWN : -6)



SECT "G"- "G"



9P ONLY



SECT "H"- "H"




Fig-1

OBSOLETED	BLACK			44.0	40.50	20.25	25.60		9	2-292175-9
				44.0	40.4	20.2	22.9		8	2- -8
				32.0	28.4	14.2	20.9		7	2- -7
				32.0	28.4	14.2	18.9		6	2- -6
				32.0	28.4	14.2	16.9		5	2- -5
				32.0	28.4	14.2	14.9		4	2- -4
				32.0	28.4	14.2	12.9		3	2- -3
		WITH	32.0	28.4	14.2	10.9	700	2	2-292175-2	
	NATURAL			44.0	40.50	20.25	25.60		9	292175-9
				44.0	40.4	20.2	22.9		8	-8
				32.0	28.4	14.2	20.9		7	-7
				32.0	28.4	14.2	18.9		6	-6
				32.0	28.4	14.2	16.9		5	-5
				32.0	28.4	14.2	14.9		4	-4
				32.0	28.4	14.2	12.9		3	-3
WITH		32.0	28.4	14.2	10.9	700	2	292175-2		
COLOR	PLATE	D	C	B	A	QTY/ REEL	POS	TAPING P/N		


NOTES:

1. PEELING RESISTANCE: 0.196N(20gf)-0.686N(70gf)
SPEED: 300mm/min

TOLERANCE UNLESS
OTHERWISE SPECIFIED

10>*	±0.2
30>*>10	±0.25
100>*>30	±0.3
ANGLE	±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	

DWN JACH HOU 19SEP10

CHK MARTIN LI 19SEP10

APVD STEVEN YAO 19SEP10

PRODUCT SPEC

108-60016

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

ON TAPING (EMBOSS)
TE CT CONNECTOR POST HEADER ASS'Y
(BOX-V SMT W/O BOSS & W/TAI)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C=292175	-

SCALE	SHEET	REV
1:1	1 OF 3	B2

