



# TAOGLAS®



## Datasheet

### 78 mm Miniature Speaker – 8 Ohm – IP67

*Part No:*  
**SPKM.78.8.B**

*Description:*

78mm Miniature Speaker - 8 Ohm 5W RMS – IP67

Compact design for integration in a wide range of products

*Features:*

8 Ohm Impedance

Rated Input Power 5W RMS

Max Input Power 8W peak

High Sensitivity

Dimensions: Ø78 x 27.5mm

Connector: Wire Lead

RoHS & Reach Compliant

|                                   |    |
|-----------------------------------|----|
| 1. Introduction                   | 3  |
| 2. Specifications                 | 4  |
| 3. Speaker Measurement Conditions | 6  |
| 4. Speaker Characteristics        | 7  |
| 5. Mechanical Drawing             | 8  |
| 6. Packaging                      | 9  |
| <hr/>                             |    |
| Changelog                         | 10 |

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.



## 1. Introduction



Featuring a compact design, enabling ease of integration in a wide range of electronics products, including IoT devices, with high levels of long-term reliability and best in class performance Taoglas products are known for.

Our 78 mm Miniature Speake has an IP67 rating, offers 100 Hz - 10 kHz frequency response, 98 dB sensitivity, 8 Ohm impedance, 5W RMS and 8W Peak power handling. Proven performance in demanding applications where accurate reproduction of voice communications is required. Taoglas added speakers to our product portfolio to provide both reliable connectivity and high-quality audio solutions from one trusted company.

Please contact your regional Taoglas customer support team for more information or installation guidelines.

## 2. Specifications

| Electroacoustic      |                                                                                                                        |
|----------------------|------------------------------------------------------------------------------------------------------------------------|
| Sound Pressure Level | 98 dB SPL ( $\pm 3$ dB) @ 1000Hz (0 dB SPL = 20 $\mu$ Pa)<br>Measuring Condition: 0.5W (Sine wave) @ 0.1 m with baffle |
| Impedance            | 8 $\Omega$ ( $\pm 15\%$ ) @ 1 kHz with 1 V input signal and without baffle in place                                    |
| Frequency Response   | 100 Hz – 10 kHz                                                                                                        |
| Resonant Frequency   | 500 Hz ( $\pm 15\%$ ) Typical frequency @ 1 V                                                                          |
| Nominal Input Power  | 5 Watts                                                                                                                |
| Maximum Input Power  | 8 Watts                                                                                                                |
| Distortion           | Less than 5% @ 1KHz, with input levels up to 2 V RMS                                                                   |
| Mechanical           |                                                                                                                        |
| Height               | 27.5 mm                                                                                                                |
| Diameter             | 78 mm                                                                                                                  |
| Weight               | 0.30 Kg                                                                                                                |
| Connector            | Wire leads - AWG#32 (UL1571)                                                                                           |
| Material             | PEI diaphragm with Neodymium Magnet, (without enclosure)                                                               |
| Environmental        |                                                                                                                        |
| Temperature Range    | -10°C to 65°C                                                                                                          |
| Humidity             | Non-condensing up to 95% Relative Humidity @ up to 65°C                                                                |

| Reliability Testing    |                                                                    |                     |
|------------------------|--------------------------------------------------------------------|---------------------|
| High Temperature Test  | High Temp                                                          | +80°C (±2°C)        |
|                        | Duration                                                           | 96 Hours            |
| Low Temperature Test   | Low Temp                                                           | -40°C (±2°C)        |
|                        | Duration                                                           | 96 Hours            |
| Heat Shock Test        | High Temp                                                          | +65°C (±2°C)        |
|                        | Low Temp                                                           | -10°C (±2°C)        |
|                        | Changeover time                                                    | <30 Seconds         |
|                        | Duration                                                           | 1 Hour              |
|                        | Cycle                                                              | 100 cycles          |
| Humidity Test          | Temp                                                               | +45°C (±2°C)        |
|                        | Relative humidity                                                  | 90 - 95 %           |
|                        | Duration                                                           | 96 Hours            |
| Temperature Cycle Test | Temp                                                               | -10°C to +65°C      |
|                        | Duration                                                           | 24 minutes          |
|                        | Temperature gradient                                               | 1°C to 3°C / minute |
|                        | Cycle                                                              | 25 cycles           |
| Drop Test              | Mounted with dummy set mass                                        | 100 g               |
|                        | Height                                                             | 1 m                 |
|                        | Cycle                                                              | 6 cycles            |
| Load Test              | White noise (EIA filter) for 96 hours @ 0.8 W (2.53 V) input power |                     |
|                        | White noise (EIA filter) for 1 minute @ 1.0 W (2.83 V) input power |                     |


\* SPL (Sound Pressure Level) as specified did not deviate more than ±3 dB from initial value, with no significant damage after testing.

## 3. Speaker Measurement Conditions

### 3.1 Conditions



| Standard Test Fixture Conditions |                 |
|----------------------------------|-----------------|
| Input Power                      | 0.5 Watts (2 V) |
| Mode                             | TSR             |
| Potentiometer Range              | 50 dB           |
| Sweep Time                       | 0.5 seconds     |

### 3.2 Measurement Fixture Diagram




## 4. Speaker Characteristics

### 4.1 SPL vs. Frequency and Impedance vs. Frequency




## 5. Mechanical Drawing (Units: mm)




| ITEM | DESCRIPTIONS | SPEC.                 | QTY | REMARK    |
|------|--------------|-----------------------|-----|-----------|
| 1    | Frame        | 78 mm                 | 1   | Fe        |
| 2    | Voice coil   | $8\Omega$             | 1   | Copper    |
| 3    | Magnet       | $\phi 45 \times 8$ mm | 1   | (Nd-Fe-B) |
| 4    | Diaphragm    | $34.8 \times 75\mu$   | 1   | PET       |
| 5    | Lead wire    |                       | 2   |           |

## 6. Packaging


1 pcs SPKM.78.8.B per Blister  
Dimensions – 100 x 100 x 28.3mm



40pcs SPKM.78.8.B per EPE Tray



120 pcs SPKM.78.8.B per Carton  
Dimensions – 535 x 325 x 360mm



Changelog for the datasheet

SPE-23-8-086 – SPKM.78.8.A

|                  |                 |
|------------------|-----------------|
| Revision: D      |                 |
| Date:            | 11-04-2023      |
| Changes:         | Initial Release |
|                  |                 |
| Changes Made by: | Carlos Gomes    |

Previous Revisions

|  |  |
|--|--|
|  |  |
|  |  |
|  |  |
|  |  |

|  |  |
|--|--|
|  |  |
|  |  |
|  |  |
|  |  |

|  |  |
|--|--|
|  |  |
|  |  |
|  |  |
|  |  |

|  |  |
|--|--|
|  |  |
|  |  |

|  |  |
|--|--|
|  |  |
|  |  |

|  |  |
|--|--|
|  |  |
|  |  |

|  |  |
|--|--|
|  |  |
|  |  |

|  |  |
|--|--|
|  |  |
|  |  |

|  |  |
|--|--|
|  |  |
|  |  |

|  |  |
|--|--|
|  |  |
|  |  |



[www.taoglas.com](http://www.taoglas.com)

