

Short circuit rugged 1200 V TRENCHSTOP™ IGBT 7 technology

Features


- $V_{CE} = 1200 \text{ V}$
- $I_C = 120 \text{ A}$
- Low saturation voltage $V_{CEsat} = 2.0 \text{ V}$ at $T_{vj} = 175^\circ\text{C}$
- Short circuit ruggedness $8 \mu\text{s}$
- Wide range of dv/dt controllability
- Complete product spectrum and PSpice Models: <http://www.infineon.com/igbt/>

Potential applications

- Industrial power supplies
- Solar

Product validation

- Qualified for industrial applications according to the relevant tests of JEDEC47/20/22



Halogen-free



Lead-free




Green



RoHS

Description



Type	Package	Marking
IGQ120N120S7	PG-TO247-3-PLUS-NN3.7	G120MS7



Table of contents

	Description	1
	Features	1
	Potential applications	1
	Product validation	1
	Table of contents	2
1	Package	3
2	IGBT	3
3	Characteristics diagrams	6
4	Package outlines	11
5	Testing conditions	12
	Revision history	13
	Disclaimer	14

1 Package

Table 1 Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Internal emitter inductance measured 5 mm (0.197 in.) from case	L_E			13		nH
Storage temperature	T_{stg}		-55		150	°C
Soldering temperature	T_{sold}	wave soldering 1.6 mm (0.063 in.) from case for 10 s			260	°C
Thermal resistance, junction-ambient	$R_{th(j-a)}$				40	K/W
IGBT thermal resistance, junction-case	$R_{th(j-c)}$			0.11	0.15	K/W

2 IGBT

Table 2 Maximum rated values

Parameter	Symbol	Note or test condition		Values	Unit
Collector-emitter voltage	V_{CE}	$T_{vj} \geq 25\text{ °C}$		1200	V
DC collector current, limited by T_{vjmax}	I_C	limited by bondwire	$T_c = 25\text{ °C}$	216	A
			$T_c = 100\text{ °C}$	144	
Pulsed collector current, t_p limited by T_{vjmax}	I_{Cpulse}			360	A
Turn-off safe operating area		$V_{CE} \leq 1200\text{ V}, T_{vj} \leq 175\text{ °C}$		360	A
Gate-emitter voltage	V_{GE}			±20	V
Transient gate-emitter voltage	V_{GE}	$t_p \leq 0.5\text{ }\mu\text{s}, D < 0.001$		±25	V
Short-circuit withstand time	t_{SC}	$V_{CC} \leq 600\text{ V}, V_{GE} = 15\text{ V}$, Allowed number of short circuits < 1000, Time between short circuits $\geq 1.0\text{ s}, T_{vj} = 150\text{ °C}$		8	μs
Power dissipation	P_{tot}	$T_{vj} \leq 175\text{ °C}$	$T_c = 25\text{ °C}$	1004	W
			$T_c = 100\text{ °C}$	502	

Table 3 Characteristic values

Parameter	Symbol	Note or test condition		Values			Unit
				Min.	Typ.	Max.	
Collector-emitter saturation voltage	V_{CEsat}	$I_C = 120\text{ A}, V_{GE} = 15\text{ V}$	$T_{vj} = 25\text{ °C}$		1.65	2	V
			$T_{vj} = 175\text{ °C}$		2		

(table continues...)

Table 3 (continued) Characteristic values

Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Gate-emitter threshold voltage	V_{GEth}	$I_C = 2.34 \text{ mA}$, $V_{CE} = V_{GE}$	5.1	5.7	6.5	V
Zero gate-voltage collector current	I_{CES}	$V_{CE} = 1200 \text{ V}$, $V_{GE} = 0 \text{ V}$	$T_{vj} = 25 \text{ °C}$		20	μA
			$T_{vj} = 175 \text{ °C}$		10400	
Gate-emitter leakage current	I_{GES}	$V_{CE} = 0 \text{ V}$, $V_{GE} = 20 \text{ V}$			100	nA
Transconductance	g_{fs}	$I_C = 120 \text{ A}$, $V_{CE} = 20 \text{ V}$, $T_{vj} = 175 \text{ °C}$		51		S
Short-circuit collector current	I_{SC}	$V_{CC} \leq 600 \text{ V}$, $V_{GE} = 15 \text{ V}$, $t_{SC} \leq 8 \text{ }\mu\text{s}$, Allowed number of short circuits < 1000, Time between short circuits $\geq 1.0 \text{ s}$, $T_{vj} = 150 \text{ °C}$		720		A
Input capacitance	C_{ies}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 100 \text{ kHz}$		17.3		nF
Output capacitance	C_{oes}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 100 \text{ kHz}$		325		pF
Reverse transfer capacitance	C_{res}	$V_{CE} = 25 \text{ V}$, $V_{GE} = 0 \text{ V}$, $f = 100 \text{ kHz}$		80		pF
Gate charge	Q_G	$I_C = 120 \text{ A}$, $V_{GE} = 15 \text{ V}$, $V_{CC} = 960 \text{ V}$		710		nC
Turn-on delay time	$t_{d(on)}$	$V_{CC} = 600 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{G(on)} = 1.3 \text{ }\Omega$, $R_{G(off)} = 1.3 \text{ }\Omega$	$T_{vj} = 25 \text{ °C}$, $I_C = 120 \text{ A}$		44	ns
			$T_{vj} = 175 \text{ °C}$, $I_C = 120 \text{ A}$		42	
Rise time (inductive load)	t_r	$V_{CC} = 600 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{G(on)} = 1.3 \text{ }\Omega$, $R_{G(off)} = 1.3 \text{ }\Omega$	$T_{vj} = 25 \text{ °C}$, $I_C = 120 \text{ A}$		34	ns
			$T_{vj} = 175 \text{ °C}$, $I_C = 120 \text{ A}$		35	
Turn-off delay time	$t_{d(off)}$	$V_{CC} = 600 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{G(on)} = 1.3 \text{ }\Omega$, $R_{G(off)} = 1.3 \text{ }\Omega$	$T_{vj} = 25 \text{ °C}$, $I_C = 120 \text{ A}$		215	ns
			$T_{vj} = 175 \text{ °C}$, $I_C = 120 \text{ A}$		256	
Fall time (inductive load)	t_f	$V_{CC} = 600 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{G(on)} = 1.3 \text{ }\Omega$, $R_{G(off)} = 1.3 \text{ }\Omega$	$T_{vj} = 25 \text{ °C}$, $I_C = 120 \text{ A}$		106	ns
			$T_{vj} = 175 \text{ °C}$, $I_C = 120 \text{ A}$		200	
Turn-on energy	E_{on}	$V_{CC} = 600 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{G(on)} = 1.3 \text{ }\Omega$, $R_{G(off)} = 1.3 \text{ }\Omega$	$T_{vj} = 25 \text{ °C}$, $I_C = 120 \text{ A}$		10.3	mJ
			$T_{vj} = 175 \text{ °C}$, $I_C = 120 \text{ A}$		12.6	

(table continues...)

Table 3 (continued) Characteristic values


Parameter	Symbol	Note or test condition	Values			Unit
			Min.	Typ.	Max.	
Turn-off energy	E_{off}	$V_{CC} = 600 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{G(on)} = 1.3 \Omega$, $R_{G(off)} = 1.3 \Omega$		5.72		mJ
				9.5		
Total switching energy	E_{ts}	$V_{CC} = 600 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_{G(on)} = 1.3 \Omega$, $R_{G(off)} = 1.3 \Omega$		16.1		mJ
				22.1		
Operating junction temperature	T_{vj}		-40		175	°C

Note: *Electrical Characteristic, at $T_{vj} = 25^\circ\text{C}$, unless otherwise specified.*
For optimum lifetime and reliability, Infineon recommends operating conditions that do not exceed 80% of the maximum ratings stated in this datasheet.
Dynamic test circuit, parasitic inductance $L_\sigma = 30 \text{ nH}$, $C_\sigma = 18 \text{ pF}$. Energy losses include “tail” and diode (IKQ120N120CS7) reverse recovery

3 Characteristics diagrams


Reverse bias safe operating area

$I_C = f(V_{CE})$
 $T_{vj} \leq 175\text{ °C}, V_{CE} \leq 1200\text{ V}$




Typical output characteristic

$I_C = f(V_{CE})$
 $T_{vj} = 25\text{ °C}$




Typical output characteristic

$I_C = f(V_{CE})$
 $T_{vj} = 175\text{ °C}$



Typical transfer characteristic


$I_C = f(V_{GE})$
 $V_{CE} = 20\text{ V}$



Typical collector-emitter saturation voltage as a function of junction temperature


$$V_{CEsat} = f(T_{vj})$$

$$V_{GE} = 15 \text{ V}$$


Gate-emitter threshold voltage as a function of junction temperature


$$V_{GEth} = f(T_{vj})$$

$$I_C = 2.34 \text{ mA}$$


Typical switching times as a function of collector current


$$t = f(I_C)$$

$$V_{CC} = 600 \text{ V}, T_{vj} = 175 \text{ °C}, V_{GE} = 0/15 \text{ V}, R_G = 1.3 \text{ } \Omega$$


Typical switching times as a function of gate resistor

$$t = f(R_G)$$


$$I_C = 120 \text{ A}, V_{CC} = 600 \text{ V}, T_{vj} = 175 \text{ °C}, V_{GE} = 0/15 \text{ V}$$



Typical switching times as a function of junction temperature

$$t = f(T_{vj})$$


$I_C = 120 \text{ A}$, $V_{CC} = 600 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_G = 1.3 \Omega$



Typical switching energy losses as a function of collector current

$$E = f(I_C)$$


$V_{CC} = 600 \text{ V}$, $T_{vj} = 175 \text{ °C}$, $V_{GE} = 0/15 \text{ V}$, $R_G = 1.3 \Omega$



Typical switching energy losses as a function of gate resistor

$$E = f(R_G)$$


$I_C = 120 \text{ A}$, $V_{CC} = 600 \text{ V}$, $T_{vj} = 175 \text{ °C}$, $V_{GE} = 0/15 \text{ V}$



Typical switching energy losses as a function of junction temperature


$$E = f(T_{vj})$$

$I_C = 120 \text{ A}$, $V_{CC} = 600 \text{ V}$, $V_{GE} = 0/15 \text{ V}$, $R_G = 1.3 \Omega$




Typical switching energy losses as a function of collector emitter voltage


$$E = f(V_{CE})$$

 $I_C = 120 \text{ A}, T_{vj} = 175 \text{ °C}, V_{GE} = 0/15 \text{ V}, R_G = 1.3 \text{ } \Omega$

Typical gate charge


$$V_{GE} = f(Q_G)$$

 $I_C = 120 \text{ A}$

Typical capacitance as a function of collector-emitter voltage

$$C = f(V_{CE})$$


 $f = 100 \text{ kHz}, V_{GE} = 0 \text{ V}$

Typical short circuit collector current as a function of gate-emitter voltage

$$I_{C(SC)} = f(V_{GE})$$

 $T_{vj} = 150 \text{ °C}, V_{CC} \leq 600 \text{ V}$



Short circuit withstand time as a function of gate-emitter voltage

$t_{SC} = f(V_{GE})$
 $T_{vj} \leq 150\text{ }^{\circ}\text{C}$, $V_{CC} \leq 600\text{ V}$



IGBT transient thermal impedance as a function of pulse width

$Z_{th(j-c)} = f(t_p)$
 $D = t_p/T$



4 Package outlines




Figure 1

5 Testing conditions




Figure 2

Revision history

Document revision	Date of release	Description of changes
0.10	2022-05-06	Target datasheet
1.00	2022-12-05	Final datasheet
1.10	2023-01-23	Correction of boundary condition of diagrams $I_{C(SC)} = f(V_{GE})$ and $t_{SC} = f(V_{GE})$ Change of product outline drawing on page 11

Trademarks

All referenced product or service names and trademarks are the property of their respective owners.

Edition 2023-01-23

Published by

Infineon Technologies AG
81726 Munich, Germany

© 2023 Infineon Technologies AG
All Rights Reserved.

Do you have a question about any aspect of this document?

Email: erratum@infineon.com

Document reference
IFX-ABD289-003

Important notice

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenhheitsgarantie").

With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

Warnings

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.