



Part Number : 511020400

Product Description : 2.50mm Pitch Mini-Lock Wire-to-Board Housing, Friction Lock, 4 Circuits, Natural

Series Number : 51102


Status : Obsolete

Product Category : Connector Housings

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Connector Housings

Series	51102
Description	2.50mm Pitch Mini-Lock Wire-to-Board Housing, Friction Lock, 4 Circuits, Natural
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Family	Mini-Lock Wire-to-Board Connector System
Product Name	Mini-Lock
UPC	800754365468

Physical

Circuits (maximum)	4
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	307.300/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

This document was generated on Jul 30, 2024