



Part Number : [2014441108](#)
Product Description : Nano-Fit Plug Housing, TPA Capable, 2.50mm Pitch, Dual Row, 8 Circuits, Black, Glow-Wire Capable
Series Number : 201444
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

- [2014441108 sd.pdf](#)
- [2014441000-PK-000.pdf](#)

3D Models and Design Files

- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [AS-105300-100-001.pdf](#)
- [2014471000-PS-000.pdf](#)
- [2014471000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	201444
Description	Nano-Fit Plug Housing, TPA Capable, 2.50mm Pitch, Dual Row, 8 Circuits, Black, Glow-Wire Capable
Application	Power, Wire-to-Wire
Product Name	Nano-Fit
UPC	191130026531

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	8
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	Yes

Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.923/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.50mm
Pitch - Termination Interface	2.50mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Nano-Fit Receptacle Housing, TPA Capable, 2.50mm Pitch, Dual Row, 8 Circuits, Black, Glow-Wire Capable	<u>1053081208</u>
Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Cable Assembly, Dual Row, 150.00mm Length, 8 Circuits, Black	<u>451300801</u>
Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Cable Assembly, Dual Row, 300.00mm Length, 8 Circuits, Black	<u>451300803</u>
Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Cable Assembly, Dual Row, 1.0m Length, 8 Circuits, Black	<u>451300810</u>
Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, Matte Tin (Sn) Plating, 500.00mm Length, 8 Circuits, Black	<u>2451300805</u>
Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, Matte Tin	<u>2451300810</u>

(Sn) Plating, 1.0m Length, 8 Circuits, Black	
Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, Matte Tin (Sn) Plating, 2.0m Length, 8 Circuits, Black	<u>2451300820</u>
Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, Matte Tin (Sn) Plating, 3.0m Length, 8 Circuits, Black	<u>2451300830</u>
Nano-Fit-to-Nano-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, Matte Tin (Sn) Plating, 5.0m Length, 8 Circuits, Black	<u>2451300850</u>

Use with Part(s)

Description	Part Number
Nano-Fit Male Crimp Terminals	<u>201447</u>
Nano-Fit Terminal Position Assurance (TPA) Retainers	<u>105325</u>

This document was generated on May 13, 2026