





Color: ■ black



Dimensions in mm



Dimensions in mm



Strain relief housing *WINSTA*® MIDI 7-pole

The strain relief housing from the *WINSTA*® MIDI product line is the best solution for trouble-free installation. An extensive range of accessories complements the *WINSTA*® product line from WAGO. The *WINSTA*® MIDI Pluggable Connection System with Push-in CAGE CLAMP® spring pressure connection technology facilitates safe electrification. Due to the integrated test slot, connections can be checked even when they are plugged in. This saves time, labor, and money. The strip length is 55 mm.

Lower costs through fast commissioning and elimination of service expenses – solutions from *WINSTA*® MIDI

The *WINSTA*® Pluggable Connection System allows pluggable electrical installation. This saves time, lowers costs, and reduces the need for servicing. Take advantage of the pluggable version of our maintenance-free spring pressure connection technology too! Plan your installation with with protection against mismatching from WAGO.

- for automation controllers
- quick replacement of defective units during ongoing operation

Connection data

| Connection 1 | |
|-------------------------------------|-------------|
| Pole number | 7 |
| Connectable sheathed cable diameter | 8 ... 15 mm |
| Strip length (outer insulation) | 55 mm |

Physical data

| | |
|-------------|------------------------|
| Pin spacing | 10 mm / 0.394 inches |
| Width | 43.1 mm / 1.697 inches |
| Height | 32.9 mm / 1.295 inches |
| Depth | 45 mm / 1.772 inches |

Material data

| | |
|------------------------------------|--|
| Note (material data) | Information on material specifications can be found here |
| Color | black |
| Insulation material (main housing) | Polyamide (PA66) |
| Flammability class per UL94 | V0 |
| Fire load | 0.517 MJ |
| Weight | 12.9 g |

Environmental requirements

| | |
|--|--|
| Processing temperature | -5 ... +40 °C |
| Continuous operating temperature | -35 ... +85 °C |
| Note on continuous operating temperature | Insulating parts for temperatures ≤ 105 °C |

Commercial data

| | |
|-----------------------|---------------|
| PU (SPU) | 200 pcs |
| Packaging type | Box |
| Country of origin | DE |
| GTIN | 4045454554453 |
| Customs tariff number | 39269097900 |



| Product classification | |
|------------------------|----------------------|
| UNSPSC | 39121421 |
| eCl@ss 10.0 | 27-44-06-92 |
| eCl@ss 9.0 | 27-44-06-92 |
| ETIM 9.0 | EC002863 |
| ETIM 8.0 | EC002863 |
| ECCN | NO US CLASSIFICATION |

| Environmental Product Compliance | |
|----------------------------------|------------------------|
| RoHS Compliance Status | Compliant,No Exemption |

| Approvals / Certificates | |
|-----------------------------------|--|
| Approvals for marine applications | |



| Approval | Standard | Certificate Name |
|-----------------------|-----------|------------------|
| LR Lloyds Register | IEC 61984 | LR22429487TA |

| Downloads | |
|---|--|
| Environmental Product Compliance | |
| Compliance Search | |
| Environmental Product Compliance 770-507/047-000 | |

| Documentation | | | |
|-----------------|------------|-----------------|--|
| Bid Text | | | |
| 770-507/047-000 | 19.02.2019 | xml 2.82 KB | |
| 770-507/047-000 | 06.01.2015 | doc 23.50 KB | |

| CAD/CAE-Data | |
|---------------------------------|-----------------------------------|
| CAD data | CAE data |
| 2D/3D Models 770-507/047-000 | WSCAD Universe 770-507/047-000 |



| |
|--------------------------|
| 1 Compatible Products |
| 1.1 Optional Accessories |
| 1.1.1 Marking |
| 1.1.1.1 Marking strip |



Item No.: 210-333
Marking strips; as a DIN A4 sheet; Strip width 6 mm; Strip length 182 mm; plain; Self-adhesive; white

| |
|--------------------|
| Installation Notes |
| Application |



Snap-on type strain relief housings for:

- 3-pole socket or plug
- 4-pole socket or plug

"Flying leads"
(NOTICE: Only use locking levers on upper position!)

"Flying leads"