
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION -,- .
© COPYRIGHT - By - ALL RIGHTS RESERVED.


LOC	DIST
—	—


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	-	-	—	—



NOTES:
1. RATED CURRENT:2.0AMP.
2. CONTACT RESISTANCE:20mΩ MAX.
3. WITHSTAND VOLTAGE:500V AC/DC
4. INSULATION RESISTANCE:1000MΩ MIN.
5. OPERATION TEMPERATURE:−40℃ TO +105℃
6. CONTACT MATERIAL:COPPER ALLOY
7. INSULATOR MATERIAL:PA9T UL94V−0 BK
8. CONTACT PLATING: "ZONE Ⅰ" 10u'' AU PLATING OVER NI
   "ZONE Ⅱ" GOLDFLASH OVER NI







RECOMMENDED P.C.B LAYOUT
(COMPONENT SIDE)

				40	4−2271598−0
				20	2−2271598−0
				8	2271598−8
				6	2271598−6
				4	2271598−4
TUBE	3.40	8.76	3.40	2	2271598−2
PACKAGING	C	B	A	POS	PN

PRODUCT FAMILY TABLE

2271598

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± 0.30
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL -
FINISH -

DWN BO GAO 16APR2015
CHK KOBBY ZHAO -
APVD XIANG XU -
PRODUCT SPEC 108−137777
APPLICATION SPEC —
WEIGHT —

TE Connectivity

NAME
AMPMODU, PIN HDR, 2.00PITCH
DOUBLE ROW, DUAL HOUSING
−

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-2271598	—

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV A

1471−9 (3/11)

Downloaded from Arrow.com.