

KLIPPON STB 5 MS HT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Abbildung ähnlich

Ideally suited for the energy, process and transportation industries, the Klippon® STB enclosure series is the perfect complement to our existing Klippon® enclosure portfolio. Enclosures in this series are approved according to international standards such as e.g. the Lloyds Register and EN62208.

- Sheet steel 1.0330, powder-coated in RAL 7032
- Comes with a standard seal that is resistant to high temperatures - extended temperature range of -60°C to +120°C
- Approved according to Lloyds Register
- Flexible options for fastening the internal mounting rail
- IP66 protection
- Secure, permanent function of the seal is ensured by seal compression protection
- Earthing stud in the cover and base of the enclosure
- Laser cut weld seams for increased quality
- Already welded-on mounting feet guarantee optimum enclosure installation

Weidmüller can manufacture and supply this enclosure - according to customer specifications - fitted with all necessary terminals and cable glands.



General ordering data

| | |
|------------|---|
| Version | Klippon STB (Small Terminal Box), Empty enclosure, Sheet steel enclosure, Height: 160 mm, Width: 380 mm, Depth: 120 mm, Basic material: Sheet steel, Powder-coated, Pebble grey |
| Order No. | 1025040000 |
| Type | KLIPPON STB 5 MS HT |
| GTIN (EAN) | 4032248745258 |
| Qty. | 1 items |

KLIPPON STB 5 MS HT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

| | | | |
|-----------------------------|--------|----------------------------|--------------|
| Depth | 120 mm | Depth (inches) | 4.7244 inch |
| Height | 160 mm | Height (inches) | 6.2992 inch |
| Width | 380 mm | Width (inches) | 14.9606 inch |
| Mounting dimension - height | 80 mm | Mounting dimension - width | 405 mm |
| Net weight | 3974 g | | |

Temperatures

Operating temperature -60 °C...120 °C

Environmental Product Compliance

RoHS Compliance Status Compliant without exemption
 REACH SVHC No SVHC above 0.1 wt%

Cable glands, left

| | | | |
|-----|----|-----|----|
| M63 | 1 | M12 | 20 |
| M50 | 1 | M16 | 12 |
| M32 | 4 | M25 | 6 |
| M20 | 12 | M40 | 2 |

Cable glands, right

| | | | |
|-----|----|-----|----|
| M25 | 6 | M63 | 1 |
| M16 | 12 | M40 | 2 |
| M50 | 1 | M32 | 4 |
| M20 | 12 | M12 | 20 |

Cable glands, top/bottom

| | | | |
|-----|----|-----|----|
| M20 | 30 | M12 | 64 |
| M63 | 2 | M40 | 6 |
| M32 | 10 | M25 | 16 |
| M50 | 4 | M16 | 33 |

Certificate numbers enclosure

| | | | |
|---|---------------------------|-----------------------------|--------------|
| Declaration of Conformity No. (DoC LVD) | DE PS2620 160412 002ISS02 | Certificate No. (LLOYDSREG) | LR23307703TA |
| Approval conditions | LR | | |

General information

| | | | |
|-----------------------------|--------|---------------------------------|--------|
| Material thickness of cover | 1.5 mm | Material thickness of enclosure | 1.5 mm |
| Operating temperature, max. | 120 °C | Operating temperature, min. | -60 °C |

KLIPPON STB 5 MS HT

Weidmüller Interface GmbH & Co. KG

 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

| | | | |
|----------------------|--|------------------------|-----------------------------|
| Lid attachment | M5 hexagonal screw with slot and 10mm distance across flats | Standards | DIN 4102-12 |
| Surface finish | Powder-coated | Impact resistance | 10 J version standard |
| Protection degree | IP66 | Basic material | Sheet steel |
| Seal material | Silicone | Integral fixing | TAS 20 rail welded to floor |
| Enclosure attachment | Welded-on mounting foot with 8-mm holes | Protection class (UL) | Type 4, Type 4X |
| Number of lid screws | 4 | Access opening: width | 362 mm |
| Flange plate | No | Max. payload | 42.56 kg |
| Lid | Yes | Access opening: height | 140 mm |
| Areas of use | Transportation, Marine engineering, Process industry, Packaging industry | | |

Housing earth

| | | | |
|----------------------------|---|----------------------------|--|
| Cross-section , max. | 25 mm ² | Earth, enclosure, cover | Welded-on M6 x 10 stainless-steel earth stud |
| Earth, enclosure, external | Welded-on M6 x 16 stainless-steel bolts | Earth, enclosure, internal | Welded-on M6 x 16 stainless-steel bolts |

horizontal assembly

| | | | |
|---|------|-----------------|------|
| Number of DIN rails and terminals (10 mm ² , horizontal) | 1x35 | WDU 16 / ZDU 16 | 1x29 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 1x68 | WDU 4 / ZDU 4 | 1x57 |
| WDU 6 / ZDU 6 | 1x44 | | |

vertical assembly

| | | | |
|-----------------------------|------|-----------------|------|
| WDU 10 / ZDU 10 | 3x12 | WDU 16 / ZDU 16 | 3x10 |
| WDU 2,5 / ZDU 2,5 / IDU 2,5 | 3x25 | WDU 4 / ZDU 4 | 3x21 |
| WDU 6 / ZDU 6 | 3x16 | | |

Important note

| | |
|---------------------|---|
| Product information | The fire rating up to E90 acc. to DIN 4102-12 depends on concrete configurations / installations (details see "Declaration of Manufacturer" in "Downloads") |
|---------------------|---|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000261 | ETIM 9.0 | EC000261 |
| ETIM 10.0 | EC000261 | ECLASS 14.0 | 27-18-01-01 |
| ECLASS 15.0 | 27-18-01-01 | | |

KLIPPON STB 5 MS HT

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Drawings

www.weidmueller.com

Dimensioned drawing

