



Part Number : [190030026](#)
Product Description : InsulKrimp Quick Disconnect,
Female, for 18-22 (0.80-0.35mm²), Mylar Tape, Tab 2.79
x 0.51mm, Salmon
Series Number : 19003
Status : Active
Product Category : Quick Disconnects
Engineering Part Number : AA-2204T



Documents and Resources

Drawings

[190030026 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[PS-19902-008-001.pdf](#)

[PS-19902-015-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19003
Description	InsulKrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm ²), Mylar Tape, Tab 2.79 x 0.51mm, Salmon
Comments	Funnel Entry
Product Name	InsulKrimp
Type	Standard Quick Disconnect
UPC	800753028821

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Closed
Color - Resin	Salmon

Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	Nylon (PA)
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	0.462/g
Orientation	Straight
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	2.79mm
Temperature Range - Operating	-65° to +105°C
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.43mm max.
Wire Size (AWG)	18, 20, 22

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	<u>192880049</u>
Mini-Mac Applicator	<u>638857000</u>

This document was generated on May 06, 2026