

MLG1005S6N2HT000



Applications	Commercial Grade
Feature	Multilayer Non-Magnetic Core (Dielectric Ceramic)
Series Type	MLG
Status	Production
Brand	TDK



Size	
Length(L)	1.00mm ± 0.05 mm
Width(W)	0.50mm ± 0.05 mm
Thickness Height	0.50mm ± 0.05 mm
Recommended Land Pattern (A)	0.50mm Nom.
Recommended Land Pattern (B)	0.40mm Nom.
Recommended Land Pattern (C)	0.50mm Nom.

Electrical Characteristics	
Inductance	6.2nH $\pm 3\%$ at 100MHz
Rated Current	600mA
DC Resistance [Typ.]	160m Ω
DC Resistance [Max.]	250m Ω
Self Resonant Frequency [Min.]	4GHz
Self Resonant Frequency [Typ.]	4.7GHz
Q [Min.]	8 at 100MHz
Q [Typ.]	11 at 100MHz





Other	
Operating Temp. Range	-55 to 125°C
Soldering Method	Reflow Iron Soldering
AEC-Q200	NO
Packing	Punched (Paper)Taping [180mm Reel, Tape width 8mm]
Package Quantity	10000pcs
Weight	0.001g

! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.

MLG1005S6N2HT000



Characteristic Graphs (This is reference data, and does not guarantee the products characteristics.)



! Images are for reference only and show exemplary products.


! This PDF document was created based on the data listed on the TDK Corporation website.

! All specifications are subject to change without notice.

MLG1005S6N2HT000



Associated Images



! Images are for reference only and show exemplary products.
! This PDF document was created based on the data listed on the TDK Corporation website.
! All specifications are subject to change without notice.