

Technical drawing of a mechanical assembly. The drawing shows a cross-section of a component with a central threaded section. Dimensions are provided in inches and millimeters:

- Overall length: 13.10 [.516]
- Distance from left end to start of thread: 4.80 [.189]
- Distance from left end to end of thread: 3.00 [.118]

STAMP (IF ANY)

$\phi 7.80$ [.307]



11.10 [.437] REF.

$\phi 3.90$ [.154]

7.90 [.311]

$\phi 5.60$ [.220]

29.10 [1.146] REF.



- | | | | | |
|---|-------------|-------------|------------|-----|
| 8 | FERRULE | BRASS | NICKEL | 1 |
| 7 | CONTACT PIN | BRASS | GOLD | 1 |
| 6 | BARREL | BRASS | NICKEL | 1 |
| 5 | OUT CONTACT | BER. COPPER | GOLD | 1 |
| 4 | INSULATOR | PTFE | NATURAL | 1 |
| 3 | SPRING | SUS 301H | PASSIVATED | 1 |
| 2 | BODY | BRASS | NICKEL | 1 |
| 1 | SHELL | BRASS | NICKEL | 1 |
| | DESCRIPTION | MATERIAL | FINISH | QTY |

APPROVALS		DATE
DRAWN	M.ZHANG	09/09/10
CHECKED		
ISSUED		
SHEET	1 OF 1	
CAD FILE		
C:/CONNEX/282135-75.DWG		

PART DESCRIPTION			
1.0/2.3 PUSH-PULL CRIMP PLUG (FOR BELDEN 1505A CABLE)			
PART NO.			
282135-75			
DWG. NO.	282135-75.DWG	REV.	SCALE
		NC	NA
		A	