

P-CO - Component connector



3036796

<https://www.phoenixcontact.com/us/products/3036796>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component connector, for installing components that can be individually selected, nom. voltage: 250 V, nominal current: 6 A, connection method: Plug-in connection, pitch: 5.2 mm, depth: 33.2 mm, width: 5.1 mm, height: 24.2 mm, number of positions: 1, color: gray, mounting type: Pluggable (slot)

Your advantages

- For assembly, the spring-cage connections are opened or closed inside the plug with just one turn of a standard screwdriver
- Can be used in all disconnect terminal blocks of the range ...-TG with 5.2 mm width or wider, from the PT, ST, QTC and UT series
- The P-CO patented component plug can accommodate components quickly and reliably using spring-cage contacts
- A coding recess ensures protection against polarity reversal

Commercial data

Item number	3036796
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z3X
Catalog page	Page 416 (C-1-2019)
GTIN	4017918929145
Weight per piece (including packing)	3.693 g
Weight per piece (excluding packing)	3.65 g
Customs tariff number	85366990
Country of origin	PL

P-CO - Component connector



3036796

<https://www.phoenixcontact.com/us/products/3036796>

Technical data

Notes

Notes on operation	Components with a wire diameter from 0.5 mm up to 0.8 mm can be used
--------------------	--

Product properties

Product type	Component plug terminal block
Number of positions	1
Pitch	5.2 mm
Potentials	1


Insulation characteristics

Pollution degree	3
------------------	---

Connection data

Conductor cross section rigid	0.5 mm ² ... 0.8 mm ²
Conductor cross section flexible	0.5 mm ² ... 0.8 mm ²
Nominal current	6 A
Maximum load current	6 A (with 0.5 mm ² conductor cross section)
Nominal voltage	250 V (the voltage is determined by the component used)
Nominal cross section	0.5 mm ²

Dimensions

Dimensional drawing	
Width	5.1 mm
Height	24.2 mm
Depth	33.2 mm
Pitch	5.2 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0
Insulating material	PA
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3

P-CO - Component connector



3036796

<https://www.phoenixcontact.com/us/products/3036796>

Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	Pluggable (slot)
---------------	------------------

P-CO - Component connector


3036796

<https://www.phoenixcontact.com/us/products/3036796>



Drawings

Dimensional drawing




P-CO - Component connector

3036796

<https://www.phoenixcontact.com/us/products/3036796>



Dimensional drawing



P-CO - Component connector

3036796

<https://www.phoenixcontact.com/us/products/3036796>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3036796>



CSA

Approval ID: 2030668

P-CO - Component connector

3036796

<https://www.phoenixcontact.com/us/products/3036796>



Classifications

ECLASS

ECLASS-13.0	27250305
-------------	----------

ETIM

ETIM 9.0	EC002018
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

P-CO - Component connector

3036796

<https://www.phoenixcontact.com/us/products/3036796>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.027 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com