



HONEYWELL PART NUMBER
91SX43
PRODUCT CODE VDQ9120

REV	DOCUMENT	CHANGED BY	CHECK
3	0038450	PK 03JUN08	ASD



NOTES
1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .188±.002 CENTERS
2 - TERMINALS ARE PLATED FOR SOLDERING

RELEASE NO.
PR-17694-T
REPLACES

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 			DRAWN	SPK	04MAR08	Honeywell			
OPERATING FORCE ----- 5 OZ MAX		CONTACT ARRANGEMENT SPDT							CHECK	RJ	04MAR08				
RELEASE FORCE----- 1 OZ MIN			28 VOLTS DC RATING		115 VOLTS AC, 60 CPS		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			SIZE TYPE DRAWING NAME B I 91SX43 REV 3					
DIFFERENTIAL TRAVEL--- .005 MAX			SEA LEVEL		50,000 FT									SEA LEVEL	
OVERTRAVEL----- .004 MIN		INDUCTIVE	4 AMP	2.5 AMP	7 AMP										
		RESISTIVE	7 AMP	4 AMP	7 AMP		INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			WEIGHT:.003 LB MAX SHEET 1 OF 1					
		LAMP	2.5 AMP	2.5 AMP	2 AMP										
		APPROVALS						RASTER			SCALE -				

