



Electrical Commercial and Industrial


- Products
- Documentation & Literature
- News & Tradeshows
- Support

United States > All 3M Products > Market Segments > Electronics, Electrical, and Communications > Electrical Products > Electrical Commercial and Industrial > Products > Electrical Commercial & Industrial Products Catalog > Heat Shrink > Single (Thin) Wall Tubing > 3M™ Heat Shrink FP-301VW > 3M™ Heat Shrink Tubing FP-301VW-1/8-Black-500', 500 ft Length per spool, 1500 ft per carton

Find An Account Rep Where To Buy (Find A Distributor) Contact Us

3M™ Heat Shrink Tubing FP-301VW-1/8-Black-500', 500 ft Length per spool, 1500 ft per carton

3M ID 80610219414 UPC# 00054007084730 3M Product Number FP-301VW-1/8-BLACK-500' Print Share



3M™ Tubing FP-301VW has the same outstanding balance of electrical, physical and chemical properties as FP-301 tubing and is specially engineered for superior flame resistance. This tubing comes in a spool.

Need Help?

Questions? We can help
[Contact Us](#)

- Overview
- Documentation

Specifications

Agency Approvals	UL Recognized and CSA Certified
Color	Black
Dielectric Strength	900 Volt
Elongation	400 Percent
Expanded Inner Diameter	1/8 Inch
Flammability Rating	UL 224 VW-1 / CSA 0ft
Length	500 Linear Foot
Material	Highly Flame-Retardant, Flexible Polyolefin
Mil Spec	AMS-DTL-23053/5, Class 3
Non-Corrosive	Yes
Operating Temperature Range (Celsius)	-55 Degrees C to +135 Degrees C
Recovered Inner Diameter	1/16 Inch
Shrink Ratio	2:1
Tensile Strength	2400 Pound-Force Per Square Inch
Tubing Type	Single-Wall Polyolefin Flexible-Highly Flame Retardant
UL File Number	E-39100

