X2-3.0-0-SP-SM ✔ ACTIVE


RAYCHEM | RAYCHEM SWFR X2

TE Internal #: EM7483-000

Heat Shrink Tubing, Black, 2:1, Single Wall, Shrinks To 1.5 mm [.059 in], ZEROHAL Polyolefin, 3.4 mm [.134 in] Expanded Inside, RAYCHEM SWFR X2

View on TE.com >

Heat Shrink Tubing > SWFR-X2 Heat Shrink Tubing





Primary Product Color: **Black**

Expanded Inside Diameter (Min): **3.4 mm [.134 in]**

Recovered Inside Diameter (Max): **1.5 mm [.059 in]**

Primary Product Material: **ZEROHAL Polyolefin**

Wall Type: **Single Wall**

All SWFR-X2 Heat Shrink Tubing (21)

Features

Product Type Features

Wall Type	Single Wall
Tubing Product Type	Heat Shrink Tubing

Electrical Characteristics

Operating Voltage (Max)	.6 kV

Body Features

Fluid Type	Water
Primary Product Color	Black
Primary Product Material	ZEROHAL Polyolefin
Shrink Ratio	2:1
Flexibility	Very Flexible

Dimensions

Recovered Wall Thickness (Nominal)	.44 mm[.017 in]
Expanded Inside Diameter (Min)	3.4 mm[.134 in]
Recovered Inside Diameter (Max)	1.5 mm[.059 in]

Usage Conditions

Downloaded from Arrow.com.

Shrink Temperature (Min)	70 °C
Operating Temperature Range	-30 – 125 °C[-22 – 257 °F]
Tubing Flammability Type	Flame-Retardant
Recovery Temperature	90 °C

Operation/Application

Mechanical Resistance	Abrasion

Product Availability

Applicable Region	Global

Packaging Features

Packaging Method	Spool

Other

Meets Low Outgassing Requirements	No
Product Source	China

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

Downloaded from Arrow.com.


on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



TE Part # EG1114-000
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM SWFR X2



Heat Shrink Tubing(22)




Single Wall Tubing(22)


Customers Also Bought




TE Part #CAT-HST-SWFRX2
SWFR-X2 Heat Shrink Tubing




TE Part #206512-6
LARGE CABLE CLAMP KIT,BULK PKG




TE Part #5-1879252-8
RP 2B 7R50 0.1% 15PPM CUT LENGTH



TE Part #2176388-3
RQ 1206 10R5 0.1% 10PPM 5K RL



TE Part #4-2176458-9
CPF 1206 3R16 0.1% 25ppm 1K RL



TE Part #5-2176458-0
CPF 1206 3R24 0.1% 25ppm 1K RL

Documents

Product Drawings

Downloaded from Arrow.com.

X2-3.0-0-SP-SM

English

X2-3.0-0-SP-SM

English

Datasheets & Catalog Pages

Highly Flame-Retardant, Zero halogen, Low Recovery Temperature, Metric-Sized Heat-Shrinkable Tubing

English

Product Specifications

Application Specification

English

Downloaded from Arrow.com.