
**Product number** F14344\_FLORENCE-1R-ZT25

Family	Florence	FWHM	Asymmetric degrees
Type	Lens	Efficiency	94 %
LED	CALGD0414-M8W1	cd/lm	0.940
Color	Clear	Gerber File	Available
Diameter	19.5 x 286 mm		
Height	7.13 mm		
Style	Rectang		
Optic Material	PMMA		
Holder Material	-		
Fastening	["glue"]		
Status	Production ready		

**Product number** F14487\_FLORENCE-1R-MAXI-WG


Family	Florence	FWHM	Asymmetric degrees
Type	Lens	Efficiency	92 %
LED	CALGD0414-M8W1	cd/lm	1.050
Color	Clear	Gerber File	Available
Diameter	21.65 x 286 mm		
Height	11.04 mm		
Style	Rectang		
Optic Material	PMMA		
Holder Material	-		
Fastening	""		
Status	Production ready		

**Product number** C14530\_FLORENCE-1R-Z2T25

Family	Florence	FWHM	Asymmetric degrees
Type	Lens	Efficiency	88 %
LED	CALGD0414-M8W1	cd/lm	0.460
Color	Clear	Gerber File	Available
Diameter	19.5 x 286 mm		
Height	6.4 mm		
Style	Rectang		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Production ready		

**Product number** C14642\_FLORENCE-1R-UP

Family	Florence	FWHM	Asymmetric degrees
Type	Lens	Efficiency	90 %
LED	CALGD0414-M8W1	cd/lm	0.370
Color	Clear	Gerber File	Available
Diameter	285.6 x 19.51 mm		
Height	6.91 mm		
Style	Rectang		
Optic Material	PMMA		
Holder Material	-		
Fastening	["clips"]		
Status	Production ready		

**Product number F14468\_FLORENCE-1R-Z60**

Family	Florence	FWHM	58+121 degrees
Type	Lens	Efficiency	94 %
LED	CALGD0414-M8W1	cd/lm	0.550
Color	Clear	Gerber File	Available
Diameter	19.5 x 286 mm		
Height	7.55 mm		
Style	Rectang		
Optic Material	PMMA		
Holder Material	-		
Fastening	["clips"]		
Status	Production ready		

**Product number F14304\_FLORENCE-1R-Z90**

Family	Florence	FWHM	89+115 degrees
Type	Lens	Efficiency	93 %
LED	CALGD0414-M8W1	cd/lm	0.380
Color	Clear	Gerber File	Available
Diameter	19.5 x 286 mm		
Height	7 mm		
Style	Rectang		
Optic Material	PMMA		
Holder Material	-		
Fastening	["clips"]		
Status	Production ready		


**NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.**

## GENERAL INFORMATION

- Product series especially designed & optimized for CALGD0414-M8W1 series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:


[http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%208N%20UL94\\_Yellow%20Card.pdf](http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%208N%20UL94_Yellow%20Card.pdf)  
<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%208N%20PLEXIGLAS-Datasheet.pdf>




## Ledil F14344\_FLORENCE-1R-ZT2\_(CALGD0414-M8W1) / LDC (Linear)

Luminaire: Ledil F14344\_FLORENCE-1R-ZT2\_(CALGD0414-M8W1)


Lamps: 1 x Citizen\_CALGD0414-M8W1\_556.672lm@350mA\_P=4.0291W\_I=0.3499A




Luminaire: Ledil F14487\_FLORENCE-1R-MAXI-WG\_(CALGD0414-M8W1)  
Lamps: 1 x Citizen\_(CALGD0414-M8W1)\_556.672lm@350mA\_P=4.0291W\_I=0.3499A




Luminaire: Ledil C14530\_FLORENCE-1R-Z2T25\_(CALGD0414-M8W1)  
Lamps: 1 x Citizen\_CALGD0414-M8W1\_556.672lm@350mA\_P=4.0291W\_I=0.3499A




Luminaire: Ledil C14642 FLORENCE-1R-UP (CALGD0414-M8W1)  
Lamps: 1 x Citizen\_CALGD0414-M8W1\_533lm@350mA\_P=4.0291W\_I=0.3499A



Luminaire: Ledil F14468\_FLORENCE-1R-Z60\_(CALGD0414-M8W1)  
Lamps: 1 x CALGD0414-M8W1\_551.561lm@350mA\_P=4.0250W\_I=0.35A




Luminaire: Ledil F14304\_FLORENCE-1R-Z90\_(CALGD0414-M8W1)  
Lamps: 1 x Citizen\_CALGD0414-M8W1\_556.672lm@350mA\_P=4.0291W\_I=0.3499A




## Ledil F14344\_FLORENCE-1R-ZT2\_(CALGD0414-M8W1) / LDC (Polar)

Luminaire: Ledil F14344\_FLORENCE-1R-ZT2\_(CALGD0414-M8W1)

Lamps: 1 x Citizen\_CALGD0414-M8W1\_556.672lm@350mA\_P=4.0291W\_I=0.3499A




Luminaire: Ledil F14487\_FLORENCE-1R-MAXI-WG\_(CALGD0414-M8W1)  
Lamps: 1 x Citizen\_(CALGD0414-M8W1)\_556.672lm@350mA\_P=4.0291W\_I=0.3499A




Luminaire: Ledil C14530\_FLORENCE-1R-Z2T25\_(CALGD0414-M8W1)


Lamps: 1 x Citizen\_CALGD0414-M8W1\_556.672lm@350mA\_P=4.0291W\_I=0.3499A



Luminaire: Ledil C14642\_FLORENCE-1R-UP\_(CALGD0414-M8W1)  
Lamps: 1 x Citizen\_CALGD0414-M8W1\_533lm@350mA\_P=4.0291W\_I=0.3499A



Luminaire: Ledil F14468\_FLORENCE-1R-Z60\_(CALGD0414-M8W1)  
Lamps: 1 x CALGD0414-M8W1\_551.561lm@350mA\_P=4.0250W\_I=0.35A



Luminaire: Ledil F14304\_FLORENCE-1R-Z90\_(CALGD0414-M8W1)

Lamps: 1 x Citizen\_CALGD0414-M8W1\_556.672lm@350mA\_P=4.0291W\_I=0.3499A

