



Part number description :

10134331-XXXLF

LF: Lead Free, RoHs compliant, see note

XXX : Color ref or/and version



Note : THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES
AND OTHER COUNTRY REGULATIONS AS PER GS-47-0004

ACCESSORIES

Item	Description
DIN RAIL system - Mounting and Installation material	
10134392-001LF	Steel Omega Rail TH35x7,5mm -2mt length
10134393-001LF	Slotted Steel Omega Rail TH35x7,5mm -2mt length
10134394-001LF	Steel Omega Rail TH35x15mm -2mt length
10134395-001LF	Slotted Steel Omega Rail TH35x15mm -2mt length
10134387-001LF	Angled support bracket
10134389-001LF	End Bracket for TH35 Omega rail -Width 9mm
10134390-001LF	End Bracket for TH35 Omega rail -Width 6mm


PN	Colour	Version
10134331-001LF	grey	(A) multiple
10134331-002LF	blue	(A) multiple
10134331-003LF	yellow-green	(A) multiple

TECHNICAL DATA / DIMENSIONS

Dimensions	
Width mm	51.0
Length mm	84.0
Height mm	49.0
Mounting type (EN 60715)	Omega TH35
Panel mounting	M5 screw
Technical data	
Maximum load current	Cu 640A Al 580A
Insulating material	PA
Self-extinguishing degree acc. to UL94	V2
Nominal Voltage	690V
Nominal Current	640A
Connection data	
Conductor cross-section solid min/max	25 / 150 mm ²
Stripping length	max 20 mm
Screw – recessed Allen screw	M16 – SW6
Tightening torque: 25-35 mm ²	14 Nm
Tightening torque: 70-150 mm ²	30 Nm

APPROVALS

EN60947-7-1
690V – Cu 640A / Al 580A



Copyright FCI

PROF. FILE - REV C - 2015-06-19

10134392-001LF	Steel Omega Rail TH35x7,5mm -2mt length
10134393-001LF	Slotted Steel Omega Rail TH35x7,5mm -2mt length
10134394-001LF	Steel Omega Rail TH35x15mm -2mt length
10134395-001LF	Slotted Steel Omega Rail TH35x15mm -2mt length
10134387-001LF	Angled support bracket
10134389-001LF	End Bracket for TH35 Omega rail -Width 9mm
10134390-001LF	End Bracket for TH35 Omega rail -Width 6mm

spec ref				dir		Aymeric Soudy		29-06-2015		projection		size		scale							
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Aymeric Soudy		29-06-2015				A3		size out of scale							
ISO 406																					
ISO 1101				chr						mm		ecn no									
				appr		Aymeric Soudy		29-06-2015		product family		DIN Terminal Block		rel level							
surface  ISO 1302		linear		0.X		± 0.3				title		SCREW Terminal block Higt current 150 - Multiple		dwg no		10134331		rev		A	
				0.XX		± 0.1															
				0.XXX		± 0.05															
				angular		0°		± 2°		www.fcicom		cat. no.		-		Product customer drawing		sheet 1 of 1			

PDS: Rev :A

STATUS:Released

Printed: Jul 17, 2015