



**Part Number :** [1200868175](#)

**Product Description :** Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 5 Poles, B-Coded, Male (Straight) to Pigtail, 0.25mm<sup>2</sup> Black PVC Cable, 10.0m (32.81') Length

**Series Number :** 120086

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Part Number :** 405006E02M100

---

## Documents and Resources


### Drawings

[1200868175\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

### UKCA - Declaration of Conformity

### CE - Declaration of Conformity

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120086
Description	Nano-Change (M8) Single-Ended Cordset with Knurled Hexnut, 5 Poles, B-Coded, Male (Straight) to Pigtail, 0.25mm <sup>2</sup> Black PVC Cable, 10.0m (32.81') Length
IP Rating	IP67
Product Name	Nano-Change (M8)
Type	Single Ended
UPC	78172511664

### Electrical

Current - Maximum per Contact	3.0A
Voltage - Maximum	30V AC / 36V DC

### Physical

Cable Diameter	5.30mm (.209")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black
Connector End A	Nano-Change (M8)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail

Keyway	B-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	414.200/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-25° to +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	24

---

This document was generated on Jun 02, 2026