
Part Number : 470184002
Product Description : 1.27mm Pitch Serial ATA Host Receptacle, Mating Height 5.15mm, 0.38µm Gold (Au) Plating, Light Tin Solder Area, Surface Mount, Right-Angle, Top Mount Type, 22 Circuits, Lead-Free
Series Number : 47018
Status : Active
Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

470184002_sd.pdf

PK-47018-003-002.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

EE-47018-003-001.pdf

SP-47018-003-001.zip

Specifications

PS-67492-001-001.pdf

PS-67492-001-007.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

Downloaded from Arrow.com.

EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	47018
Description	1.27mm Pitch Serial ATA Host Receptacle, Mating Height 5.15mm, 0.38µm Gold (Au) Plating, Light Tin Solder Area, Surface Mount, Right-Angle, Top Mount Type, 22 Circuits, Lead-Free
Application	Board-to-Board, Signal
Comments	Top Mount Type
Component Type	PCB Receptacle
Product Name	Serial ATA
UPC	822350330831

Agency

CSA	LR19980
UL	E29179

Downloaded from Arrow.com.

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	15V DC

Physical

Circuits (Loaded)	22
Circuits (maximum)	22
Color - Resin	Black
Durability (mating cycles max)	500
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	1.750/g
Number of Rows	1
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.381µm
Plating min - Termination	2.032µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-35° to +85°C
Termination Interface Style	Surface Mount

Solder Process Data

Max-Duration	3

Downloaded from Arrow.com.

Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	255

Downloaded from Arrow.com.