



+ CONNECTORS

CONNECTOR HOUSINGS



✓ Active

TE CONNECTIVITY (TE)
STD TIM HOUSING MKII 3POS

RAST | RAST 5 IDC Connectors

1-1241961-8
TE Internal Number: 1-1241961-8

EU RoHS Compliant
Not Yet Reviewed for EU ELV

Connector System Wire-to-Board

Number of Positions 3

Centerline (Pitch) 5 mm [.197 in]

Row-to-Row Spacing 5 mm [.197 in]

Number of Rows 1

↓ PRODUCT DRAWING
English

↓ 3D PDF

DOCUMENTATION

Product Drawings

STANDARD TIMER HSG. RAST 5 MARK II Standard Timer Gehaeuse RAST 5 Mark II

PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

Standard Timer Connector (English Version)

PDF

English

Product Environmental Compliance

TE Material Declaration

MD_1-1241961-8_11042015229_dmtec

PDF

English

Agency Approvals

UL Report

Standard Timer Connector REPORT

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

- Connector System Wire-to-Board
- Row-to-Row Spacing 5 mm [.197 in]
- Connector Style Receptacle
- Sealable No
- Connector & Contact Terminates To Printed Circuit Board
- Connector Type Housing
- Product Type Connector

Configuration Features

- Selectively Loaded No
- Number of Positions 3
- Number of Rows 1
- Preloaded No

Electrical Characteristics

Operating Voltage (VAC) 250

Contact Features

Contact Type Socket
Shunts/Shorting Bars Without
Multiple Contact Types Without

Mechanical Attachment

Contact Retention Without

Housing Features

Centerline (Pitch) 5 mm [.197 in]
Housing Material PA 6 GF
Housing Color Natural

Dimensions

Height 25 mm [.984 in]
Width (mm) 13.9

Usage Conditions

Operating Temperature Range -40 – 105 °C [-40 – 221 °F]

Operation/Application

Halogen Free No
Assembly Integration Feature Without
For Use With Header

Identification Marking

Circuit Identification Feature Without

Industry Standards

Agency/Standard UL

Packaging Features

Packaging Quantity 200
Packaging Method Carton

PRODUCT COMPLIANCE



Statement of Compliance

Statement of Compliance
PDF

