


**Part Number :** [150210424](#)

**Product Description :** 0.50mm Pitch Premo-Flex LVDS Jumper, 102.00mm Cable Length, Gold (Au) Plating, 24 Circuits

**Series Number :** 15021

**Status :** Active

**Product Category :** Flat-Flexible Cable (FFC)



## Documents and Resources

### Drawings

[150210424 sd.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

### Specifications

[150210001-002.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Flat-Flexible Cable (FFC)
Series	15021
Description	0.50mm Pitch Premo-Flex LVDS Jumper, 102.00mm Cable Length, Gold (Au) Plating, 24 Circuits
Product Name	Premo-Flex LVDS Jumper
UPC	889056697156

### Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	30V AC

### Physical

Cable Length	102.00mm
Circuits (Loaded)	24
Contact Layout Type	A (same side)
Design Feature	High-Speed
Material - Outer Jacket	Polyester
Material - Plating Mating	Gold
Net Weight	0.600/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm

Temperature Range - Operating	-40° to +80°C
Termination Style	FFC Connector
Wire/Cable Type	Flat Cable
Wire Size (AWG)	N/A

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
0.50mm Pitch Easy-On FFC/FPC Connector, For LVDS, 6.05mm Height, Vertical, Surface Mount, ZIF, 24 Circuits	<u>5022312400</u>
0.50mm Pitch Easy-On FFC/FPC Connector, For LVDS, 2.33mm Height, Right-Angle, Surface Mount, ZIF, Bottom Contact Style, 24 Circuits	<u>5022442430</u>

---

This document was generated on May 06, 2026