

Part Number : 2153471124
Product Description : Pre-Crimped Lead Squba 3.6 Male-to-Squba 3.6 Male, Tin (Sn) Plating, 300.00mm Length, 16 AWG, Black
Series Number : 215347
Status : Active
Product Category : Power and Signal Cable Assemblies

Documents and Resources

Drawings

2153471124_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	215347
Description	Pre-Crimped Lead Squba 3.6 Male-to-Squba 3.6 Male, Tin (Sn) Plating, 300.00mm Length, 16 AWG, Black
Application	Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Squba 3.6 Terminal-to-Squba 3.6 Terminal
Keyword	Squba 3.6
Product Name	Squba
UPC	195842349742

Electrical

Current - Maximum per Contact	14.0A
Voltage - Maximum	600V

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Male-Male
Material - Metal	Copper Alloy
Material - Plating Mating	Matte Tin
Material - Resin	Modified Polystyrene
Net Weight	4.997/g
Number of Rows	1
Packaging Type	Bag

Downloaded from Arrow.com.

Pitch - Mating Interface	3.60mm
Plating min - Mating	2.540µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 11028
Wire Size (AWG)	16

Downloaded from Arrow.com.