



NCP3063DFBSTGEVB: DFN Boost Demonstration Evaluation Board

The NCP3063 Series is a higher frequency upgrade to the popular MC34063A and MC33063A monolithic DC-DC converters. These devices consist of an internal temperature compensated reference, comparator, a controlled duty cycle oscillator with an active current limit circuit, a driver and a high current output switch. This series was specifically designed to be incorporated in Step-Down, Step-Up and Voltage-Inverting applications with a minimum number of external components.



Features and Applications

Features

- Operation to 40 V Input
- Low Standby Current
- Output Switch Current to 1.5 A
- Frequency Operation of 150 kHz

Applications

- High Power LED Lighting
- Battery Chargers

Evaluation/Development Tool Information

Product	Status	Compliance	Short Description	Parts Used	Action
NCP3063DFBSTGEVB	Active	Pb-free	DFN Boost Demonstration Evaluation Board	NCP3063BMNTXG	» Contact Local Sales Office » Inventory

Technical Documents

Type	Document Title	Document ID/Size	Rev
Eval Board: BOM	NCP3063DFBSTGEVB Bill of Materials ROHS Compliant	NCP3063DFBSTGEVB_BOM_ROHS.PDF - 132.0 KB	0
Eval Board: Gerber	NCP3063DFBSTGEVB Gerber Layout Files (Zip Format)	NCP3063DFBSTGEVB_GERBER.ZIP - 30.0 KB	0
Eval Board: Schematic	NCP3063DFBSTGEVB Schematic	NCP3063DFBSTGEVB_SCHEMATIC.PDF - 28.0 KB	0
Eval Board: Test Procedure	NCP3063DFBSTGEVB Test Procedure	NCP3063DFBSTGEVB_TEST_PROCEDURE.PDF - 40.0 KB	0
Video	DFN Boost Demonstration Evaluation Board - NCP3063DFBSTGEVB	WVD17534/D	

Previously Viewed Products

Select Product...

Design Support

[Technical Documentation](#)

[Design Resources & Documents](#)

[Technical Support](#)

[Sales Support](#)

Featured Video

[DFN Boost Demonstration Evaluation Board - NCP3063DFBSTGEVB](#)



[More Videos ...](#)

