
© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	G	REVISED PER ECR-26-282233	01JUL2026	GSK	MP



AMP WIRE RANGE

8 AWG
STRANDED

1 BODY MATERIAL THK 0.991±0.051 [.039±.002]

2 FOR ø6.502[ø.256] MAX WIRE INSULATION.

△3 BODY – COPPER PER ASTM B152
INSULATION – NYLON

△4 BODY – TIN PLATE PER ASTM B-545
INSULATION – COLOR-RED

△5 STAMP AMP 8* 14 APPROX AS SHOWN.

100	LOOSE PC	324082
QTY	PACKAGE TYPE	PART NO

MAX RECOMMENDED OPERATING TEMPERATURE:
105°C [221°F]

VOLTAGE RATING:
N/A

CIRCULAR MIL AREA:
6.64–10.5mm² [13,100–20,800]
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± 0.127[.005]
4 PLC ± –
ANGLES ± –

MATERIAL △3

FINISH △4

DWN	JR RUTH	6-21-93
CHK	R. HERSEY	6-21-93
APVD	M ELLIS	6-21-93
PRODUCT SPEC	108-162357	
APPLICATION SPEC	—	
WEIGHT		

TE Connectivity

NAME
TERMINAL, RING TONGUE, TERMINYL
WIRE SIZE: 8 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-324082	—

CUSTOMER DRAWING	SCALE 4:1	SHEET 1 OF 1	REV G

1470-19 (1/15)

Downloaded from Arrow.com.