



Part Number : [757575131](#)
Product Description : MX150 Dual Row Header, Vertical, 6 Circuits, 2.5µm Tin (Sn) Plating, 16.09mm Mating Pin Length, 3.05mm PC Tail Length
Series Number : 75757
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings
[757575131_sd.pdf](#)
[PK-36518-340-001.pdf](#)

3D Models and Design Files
[757575131_stp.zip](#)

Specifications
[PS-75757-000-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Duty-To-Declare
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents
- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	75757
Description	MX150 Dual Row Header, Vertical, 6 Circuits, 2.5µm Tin (Sn) Plating, 16.09mm Mating Pin Length, 3.05mm PC Tail Length
Application	Power, Wire-to-Board, Automotive
Component Type	PCB Header
Product Name	MX150
UPC	800756794808

Electrical

Current - Maximum per Contact	17.0A
Voltage - Maximum	500V DC

Physical

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass

Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.602/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Tube
PC Tail Length	3.05mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Plating min - Mating	2.540µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	245

Mates With / Use With

Mates with Part(s)

Description	Part Number
MX150 Mat-Sealed Dual Row Female Connector Assemblies	<u>33472</u>
