



**Part Number :** [734154670](#)  
**Product Description :** SSMCX Jack, Straight, PCB  
Receptacle, Edge Mount, Brass Body, Gold (Au) Plated,  
Tray, 50 Ohms  
**Series Number :** 73413  
**Status :** Active  
**Product Category :** RF / Coaxial Connectors



## Documents & Resources

### Drawings


[734154670 sd.pdf](#)  
[895420040-000.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)  
[SOLIDWORKS](#)  
[Creo](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73413
Description	SSMCX Jack, Straight, PCB Receptacle, Edge Mount, Brass Body, Gold (Au) Plated, Tray, 50 Ohms
Application	RF
Product Name	SSMCX
Style	PCB
Type	Ultra-microminiature
UPC	822348896912

### Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

### Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	0.257/g
Orientation	Straight

Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Edge Mount
PCB Thickness - Recommended	Various
Reverse Polar	No
Wire/Cable Type	N/A

**Solder Process Data**

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	2
Max-Temp	260

---

This document was generated on Sep 18, 2025