Part Number : 783150011
Product Description : 1.00mm Pitch Aerodynamic DDR3 DIMM Socket, Very Low Profile, Vertical, Press-Fit, with Pegs, Black Housing and Latches, 0.76µm Gold (Au Plating, 2.85mm Compliant Pin Length, 2.60mm PCB Thickness, 240 Circuits, Lead-Free
Series Number : 78315
Status : Obsolete
Product Category : Memory Module Connectors



Obsolete

Documents and Resources

Drawings

783150011_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

AS-78315-001-001.pdf

PS-78315-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Downloaded from Arrow.com.

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Memory Module Connectors
Series	78315
Description	1.00mm Pitch Aerodynamic DDR3 DIMM Socket, Very Low Profile, Vertical, Press-Fit, with Pegs, Black Housing and Latches, 0.76µm Gold (Au Plating, 2.85mm Compliant Pin Length, 2.60mm PCB Thickness, 240 Circuits, Lead-Free
Component Type	Socket
JEDEC Outline	SO-012
Product Name	DDR3 DIMM
UPC	884982126671

Agency

CSA	LR19980
UL	E29179

Electrical

Obsolete

Downloaded from Arrow.com.

Current - Maximum per Contact	1.0A
Voltage Key	Center
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	240
Circuits (maximum)	240
Durability (mating cycles max)	25
Entry Angle	Vertical
Flammability	94V-0
Housing Color	Black
Keying to Mating Part	Yes
Latch Color	Black
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	7.595/g
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.60mm
PC Tail Length	2.85mm
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.762µm
Plating min - Termination	0.381µm
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Solder Process Data

Lead-Free Process Capability	N/A

Obsolete

Mates With / Use With

Downloaded from Arrow.com.

Mates with Part(s)

Description	Part Number
Mates With	JEDEC Standard 1.27mm Modules

Application Tooling

Global

Description	Part Number
DDR3 DIMM Memory Module Extraction Tool	622023800

This document was generated on Apr 29, 2026

Obsolete

Downloaded from Arrow.com.