

Silicon Carbide (SiC) MOSFET - EliteSiC, 32 mohm, 650 V, M3S, D2PAK-7L

NTBG032N065M3S

$V_{(BR)DSS}$	$R_{DS(ON)}$ TYP	I_D MAX
650 V	32 mΩ @ 18 V	52 A



N-CHANNEL MOSFET



D2PAK-7L
CASE 418BJ

Features

- Typical $R_{DS(ON)}$ = 32 mΩ @ V_{GS} = 18 V
- Ultra Low Gate Charge ($Q_{G(tot)}$ = 55 nC)
- High Speed Switching with Low Capacitance (Coss = 113 pF)
- 100% Avalanche Tested
- This Device is Halide Free and RoHS Compliant with Exemption 7a, Pb-Free 2LI (on Second Level Interconnection)

Applications

- SMPS, Solar Inverters, UPS, Energy Storages, EV charging infrastructure

MAXIMUM RATINGS (T_J = 25 °C unless otherwise noted)

Parameter		Symbol	Value	Unit
Drain-to-Source Voltage		V_{DSS}	650	V
Gate-to-Source Static Voltage		V_{GS}	−10/+22.6	V
Gate-to-Source Transient Voltage	t_p < 0.5 μs, Duty Cycle ≤ 1%	V_{GS}	−11/+25	V
Continuous Drain Current	T_C = 25 °C	I_D	52	A
Power Dissipation		P_D	200	W
Continuous Drain Current	T_C = 100 °C	I_D	32	A
Power Dissipation		P_D	100	W
Pulsed Drain Current (Note 1)	T_C = 25 °C, t_P = 100 μs	I_{DM}	156	A
Continuous Source-Drain Current (Body Diode)	T_C = 25 °C, V_{GS} = −3 V	I_S	30	
	T_C = 100 °C, V_{GS} = −3 V		17	
Pulsed Source-Drain Current (Body Diode) (Note 1)	T_C = 25 °C, V_{GS} = −3 V, t_P = 100 μs	I_{SM}	127	
Single Pulse Avalanche Energy (Note 2)	I_{LPK} = 16.7 A, L = 1 mH	E_{AS}	139	mJ
Operating Junction and Storage Temperature Range		T_J, T_{stg}	−55 to 175	°C
Lead Temperature for Soldering Purposes (1/8″ from Case for 10 s)		T_L	270	

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Single pulse, limited by max junction temperature.
2. E_{AS} of 139 mJ is based on starting T_J = 25 °C, L = 1 mH, I_{AS} = 16.7 A, V_{DD} = 100 V, V_{GS} = 18 V.

MARKING DIAGRAM



BG032N065M3S = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
ZZ = Lot Traceability

ORDERING INFORMATION

Device	Package	Shipping†
NTBG032N065M3S	D2PAK-7L	800 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

© Semiconductor Components Industries, LLC, 2023

Downloaded from Arrow.com.

THERMAL CHARACTERISTICS

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction-to-Case (Note 3)	$R_{\theta JC}$	0.75	°C/W
Thermal Resistance, Junction-to-Ambient (Note 3)	$R_{\theta JA}$	40	

3. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.

RECOMMENDED OPERATING CONDITIONS

Parameter	Symbol	Value	Unit
Operation Values of Gate-to-Source Voltage	V_{GSop}	−5...−3 +18	V

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0 V, I_D = 1 mA, T_J = 25 °C	650			V
Drain-to-Source Breakdown Voltage Temperature Coefficient	$\Delta V_{(BR)DSS}/\Delta T_J$	I_D = 1 mA, Referenced to 25 °C		90		mV/°C
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} = 650 V, T_J = 25 °C			10	μA
		V_{DS} = 650 V, T_J = 175 °C (Note 5)			500	
Gate-to-Source Leakage Current	I_{GSS}	V_{GS} = −10 V, V_{DS} = 0 V	−1			μA
		V_{GS} = +22.6 V, V_{DS} = 0 V			1	
ON CHARACTERISTICS						
Drain-to-Source On Resistance	$R_{DS(ON)}$	V_{GS} = 18 V, I_D = 15 A, T_J = 25 °C		32	44	mΩ
		V_{GS} = 18 V, I_D = 15 A, T_J = 175 °C (Note 5)		49		
		V_{GS} = 15 V, I_D = 15 A, T_J = 25 °C		41		
		V_{GS} = 15 V, I_D = 15 A, T_J = 175 °C (Note 5)		52		
Gate Threshold Voltage	$V_{GS(TH)}$	V_{GS} = V_{DS}, I_D = 7.5 mA, T_J = 25 °C	2.0	2.7	4.0	V
Forward Trans-conductance	g_{FS}	V_{DS} = 10 V, I_D = 15 A (Note 5)		9.9		S
CHARGES, CAPACITANCES & GATE RESISTANCE						
Input Capacitance	C_{ISS}	V_{DS} = 400 V, V_{GS} = 0 V, f = 1 MHz (Note 5)		1409		pF
Output Capacitance	C_{OSS}			113		
Reverse Transfer Capacitance	C_{RSS}			9.0		
Total Gate Charge	$Q_{G(TOT)}$	V_{DD} = 400 V, I_D = 15 A, V_{GS} = −3/18 V (Note 5)		55		nC
Gate-to-Source Charge	Q_{GS}			15		
Gate-to-Drain Charge	Q_{GD}			14		
Gate Resistance	R_G	f = 1 MHz		5.0		Ω
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	$t_{d(ON)}$	V_{GS} = −3/18 V, I_D = 15 A, V_{DD} = 400 V, R_G = 4.7 Ω, T_J = 25 °C (Note 4, 5)		8.8		ns
Turn-Off Delay Time	$t_{d(OFF)}$			31		
Rise Time	t_r			12		
Fall Time	t_f			9		
Turn-On Switching Loss	E_{ON}			33		μJ
Turn-Off Switching Loss	E_{OFF}			16		
Total Switching Loss	E_{TOT}			49		

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise specified) (continued)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
SWITCHING CHARACTERISTICS						
Turn-On Delay Time	$t_{d(ON)}$	V_{GS} = −3/18 V, I_D = 15 A, V_{DD} = 400 V, R_G = 4.7 Ω, T_J = 175 °C (Note 4, 5)		7.8		ns
Turn-Off Delay Time	$t_{d(OFF)}$			37		
Rise Time	t_r			12		
Fall Time	t_f			11		
Turn-On Switching Loss	E_{ON}			31		μJ
Turn-Off Switching Loss	E_{OFF}			25		
Total Switching Loss	E_{TOT}			56		
SOURCE-TO-DRAIN DIODE CHARACTERISTICS						
Forward Diode Voltage	V_{SD}	I_{SD} = 15 A, V_{GS} = −3 V, T_J = 25 °C		4.5	6.0	V
		I_{SD} = 15 A, V_{GS} = −3 V, T_J = 175 °C (Note 5)		4.2		
Reverse Recovery Time	t_{RR}	V_{GS} = −3 V, I_S = 15 A, dI/dt = 1000 A/μs, V_{DS} = 400 V, T_J = 25 °C (Note 5)		15.5		ns
Charge time	t_a			8.9		
Discharge time	t_b			6.6		
Reverse Recovery Charge	Q_{RR}			72		nC
Reverse Recovery Energy	E_{REC}			4.6		μJ
Peak Reverse Recovery Current	I_{RRM}			9.3		A

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. E_{ON}/E_{OFF} result is with body diode.
5. Defined by design, not subject to production test.

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 1. Output Characteristics




Figure 2. Output Characteristics




Figure 3. Transfer Characteristics




Figure 4. On-Resistance vs. Gate Voltage




Figure 5. On-Resistance vs. Drain Current




Figure 6. On-Resistance vs. Junction Temperature

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Characteristics




Figure 8. Stored Energy vs. Drain-to-Source Voltage




Figure 9. Gate Charge Characteristics




Figure 10. Reverse Conduction Characteristics




Figure 11. Reverse Conduction Characteristics




Figure 12. Safe Operating Area

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 13. Avalanche Current vs. Pulse Time (UIS)




Figure 14. Maximum Power Dissipation vs. Case Temperature




Figure 15. Inductive Switching Loss vs. Drain Current




Figure 16. Inductive Switching Loss vs. Drain Current




Figure 17. Inductive Switching Loss vs. Drain Voltage




Figure 18. Inductive Switching Loss vs. Gate Resistance

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 19. Inductive Switching Loss vs. Gate Resistance




Figure 20. Thermal Response Characteristics


Downloaded from Arrow.com.

REVISION HISTORY

Revision	Description of Changes	Date
5	Updated static and dynamic gate source voltage ratings in maximum ratings table	6/15/2026


This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.


Downloaded from Arrow.com.




D²PAK7 (TO−263−7L HV)
CASE 418BJ
ISSUE B


DATE 16 AUG 2019





LAND PATTERN RECOMMENDATION





NOTES:

A. PACKAGE CONFORMS TO JEDEC TO-263 VARIATION CB EXCEPT WHERE NOTED.
B. ALL DIMENSIONS ARE IN MILLIMETERS.
C OUT OF JEDEC STANDARD VALUE.
D. DIMENSION AND TOLERANCE AS PER ASME Y14.5-2009.
E. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR PROTRUSIONS.


DIM	MILLIMETERS		
	MIN	NOM	MAX
A	4.30	4.50	4.70
A1	0.00	0.10	0.20
b2	0.60	0.70	0.80
b	0.51	0.60	0.70
c	0.40	0.50	0.60
c2	1.20	1.30	1.40
D	9.00	9.20	9.40
D1	6.15	6.80	7.15
E	9.70	9.90	10.20
E1	7.15	7.65	8.15
e	~	1.27	~
H	15.10	15.40	15.70
L	2.44	2.64	2.84
L1	1.00	1.20	1.40
L3	~	0.25	~
aaa	~	~	0.25

GENERIC MARKING DIAGRAM*



XXXX = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
G = Pb−Free Package

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “▪”, may or may not be present. Some products may not follow the Generic Marking.



DOCUMENT NUMBER:	**98AON84234G**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.	
DESCRIPTION:	**D²PAK7 (TO−263−7L HV)**		**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

© Semiconductor Components Industries, LLC, 2018

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.